




- Features:**
- Natural convection cooling when horizontally mounted
 - Encapsulated for use in control cabinets
 - Fast and tool-free termination via lever-actuated PCB terminal blocks
 - Bounce-free switching signal (DC OK) via optocoupler
 - Parallel operation
 - Electrically isolated output voltage (SELV) per UL 60950-1; PELV per EN 60204

Technical data			
Input		Output	
Phases	2 / 3	Nominal output voltage $U_{o\ nom}$	DC 24 V (SELV)
Nominal input voltage $U_{i\ nom}$	(2 / 3) x AC 400 ... 500 V	Output voltage range	DC 22 ... 28 V (adjustable)
Input voltage range	(2 / 3) x AC 360 ... 575 V; DC 500 ... 650 V	Default setting	DC 24 V
Nominal mains frequency range	47 ... 63 Hz; 0 Hz	Nominal output current $I_{o\ nom}$	6.25 A (24 VDC)
Input current I_i	$\leq 3 \times 0.6\ A$ (400 VAC; 24 VDC / 6.25 A)	Nominal output power	150 W
Discharge current	$\leq 3.5\ mA$	Deviation	$\leq 1\ \%$
Inrush current	$\leq 25\ A$	Residual ripple	$\leq 100\ mV$ (peak-to-peak)
Power factor	≥ 0.5	Overload behavior	Constant power (in overload range: $1.15 \dots 1.4 \times I_{o\ nom}$); Shutdown and automatic restart in the event of a short circuit
Power factor correction (PFC)	Passive		
Mains failure hold-up time	$\geq 17\ ms$ (3 x 400 VAC)		
Signaling and communication		Efficiency/power losses	
Signaling	1 x LED DC OK (green) 1 x Overload LED (red) 1 x DC OK signal output (optocoupler as make contact; max. 31.2 V; 20 mA)	Power loss P_I	$\leq 18.5\ W$
Operation status indicator	Green LED (U_o) Red LED (overload)	Power loss (max.) $P_{I(max)}$	20 W
		Efficiency (typ.)	87 %
Circuit protection			
Internal fuse	3 x T 2 A / 250 VAC		
Backup fusing (required)	An external DC fuse is required for the DC input voltage.		
Backup fusing (recommended)	3 x Circuit breaker $\geq 6\ A$; Tripping characteristic: B or C Alternative: motor circuit breaker		



Safety and protection		
Isolation voltage (pri.-sec.)		DC 4.242 kV
Isolation voltage (pri.-PE)		DC 2.2 kV
Isolation voltage (sec.-PE)		DC 0.7 kV
Isolation voltage (sec.-signal)		DC 0.7 kV
Protection class		I
Protection type		IP20; per EN 60529
Resistance to reverse feed		≤ DC 30 V
Overtoltage category		II
Pollution degree		2
Transient suppression (primary)		Varistor
Short-circuit-protected		Yes
Open-circuit-proof		Yes
Parallel operation		Yes
Series operation		Yes
MTBF		> 250,000 h (per IEC 61709)

Connection data		
Connection type 1		Input/output
Connection technology		CAGE CLAMP®
WAGO connector		WAGO 2706 Series
Solid conductor		0.5 ... 6 mm² / 20 ... 10 AWG
Fine-stranded conductor		0.5 ... 6 mm² / 20 ... 10 AWG
Strip length		11 ... 12 mm / 0.43 ... 0.47 inches
Connection type 2		Signaling
Connection technology		Push-in CAGE CLAMP®
WAGO connector 2		picoMAX® 3.5 (WAGO 2091 Series)
Solid conductor 2		0.2 ... 1.5 mm² / 24 ... 14 AWG
Fine-stranded conductor 2		0.2 ... 1.5 mm² / 24 ... 14 AWG
Strip length 2		8 ... 9 mm / 0.31 ... 0.35 inches

Physical data		
Width		50 mm / 1.969 inches
Height		130 mm / 5.118 inches
Depth from upper-edge of DIN-rail		92 mm / 3.622 inches

Mechanical data		
Mounting type		DIN-35 rail

Material data		
Fire load		0 MJ
Weight		844 g



Environmental requirements	
Ambient temperature (operation)	-25 ... +70 °C
Ambient temperature (storage)	-40 ... +85 °C
Relative humidity	10 ... 95 % (no condensation permissible)
Derating	-2.5 %/K (> 50 °C; 400 VAC)
Climatic category	3K3 (per EN 60721)

Standards and specifications	
Conformity marking	CE
Standards/specifications	EN 62368-1 EN 61204-3 (Class A) UL 60950-1 UL 508 SEMI F47

Commercial data	
eCl@ss 10.0	27-04-07-01
eCl@ss 9.0	27-04-07-01
ETIM 8.0	EC002540
ETIM 7.0	EC002540
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	CN
GTIN	4050821847861
Customs tariff number	85044083900

Environmental Product Compliance	
RoHS Compliance Status	Compliant, No Exemption
SCIP notification number (Bulgaria)	6ad76c2f-5e1d-4e81-863e-4937bfb36fc5
SCIP notification number (Czech Republic)	3cb75b15-0728-4ff4-a13e-55912c975eb3

Approvals / Certificates	
General approvals	Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
EAC GZO Almaty Standart	TP TC 004/2011	EAC CoC 03078
EAC GZO Almaty Standart	TP TC 020/2011	EAC CoC 03081
UL Underwriters Laboratories Inc.	UL 508	E255817
UL Underwriters Laboratories Inc.	UL 60950-1	E255815

Approval	Standard	Certificate Name
EU-Declaration of Conformity WAGO GmbH & Co. KG	-	-
MFD for SEMI F47 WAGO GmbH & Co. KG	-	-



Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 787-738

Download icon

Documentation

Bid Text

787-738	12.07.2019	xml 7.26 KB	Download icon
787-738	12.07.2019	docx 23.13 KB	Download icon

Instruction Leaflet

Primary Switch Mode Power Supply ECO-Power	V 1.3.5 21.12.2020	pdf 280.65 KB	Download icon
--	-----------------------	------------------	---------------

CAD/CAE-Data

CAD data

2D/3D Models 787-738

Download icon

CAE data

EPLAN Data Portal 787-738

Download icon

WSCAD Universe 787-738

Download icon

ZUKEN Portal 787-738

Download icon

1 Compatible Products

1.1 Optional Accessories

1.1.1 Tool

1.1.1.1 Operating tool



[Item No.: 210-719](#)
Operating tool; Blade: 2.5 x 0.4 mm; with a partially insulated shaft



[Item No.: 210-769](#)
SCREWDRIVER; green