



Wire Protection & Management > Adhesives & Sealants > Epoxy Adhesives



Packaging Method: **Syringe**

Packaging Quantity: **2**

Heat Resistance Temperature (Max): **150 °C**

Features

Body Features

Color (Supplied)	Silver
Color (Cured)	Silver
Material Systems Code	10, 100, 25

Usage Conditions

Heat Resistance Temperature (Max)	150 °C
-----------------------------------	--------

Packaging Features

Packaging Method	Syringe
Packaging Quantity	2

Other

Curing Method	20 °C for 24 hr, 80 °C for 1 hr
Pot Life	60 minute

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)















Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # EK7289-000 202S174-25C-0	 TE Part # EK7312-000 222S152-25C-0	 TE Part # EK7282-000 202S152-25C-0	 TE Part # EK7285-000 202S163-100C-0
 TE Part # EK7301-000 222S121-25C-0	 TE Part # EK7307-000 222S132-25C-0	 TE Part # EK7313-000 222S163-100C-0	 TE Part # EK7315-000 222S163-25C-0
 TE Part # EK7318-000 222S174-25C-0	 TE Part # EK7339-000 382S023-25C-0	 TE Part # EK7344-000 382S034-25C-0	 TE Part # EK7262-000 202K132-25C-0



TE Part # EK7263-000
202K174-25C-02-0

TE Part # EK7264-000
202K185-25C-0

TE Part # EK7265-000
202S121-100C-0

TE Part # EK7268-000
202S121-25C-G13-0

TE Part # EK7271-000
202S132-100C-0

TE Part # EM4212-000
202S132-100C-01-0

TE Part # EK7274-000
202S132-25C-01-0

TE Part # EK7276-000
202S142-100C-0

Customers Also Bought

TE Part #019147-000
TXR40AB00-1007AI

TE Part #331401
SOLISTRAND RING 26-22 #6

TE Part #462673-000
55A0121-22-9/96CS2275

TE Part #EK7315-000
222S163-25C-0

TE Part #5677842003
RNF-3000-3/1-9-STK

TE Part #NB17554001
RT-375-1-X-SP

TE Part #5795953001
55M0414-28-5

TE Part #ASDD106-09PD-HE
INLINE RECEPT ASSY. ASDD 9 WAY.

TE Part #ASDD106-09PN-HE
INLINE RECEPT ASSY. ASDD 9 WAY.

TE Part #K2018276
Limit switch G13-01-1120

Documents



Datasheets & Catalog Pages

1654025_Sec5_Adhesives

English

Raychem Molded Parts Visual Guide

English

Solutions for Defense Applications Certified to VG Standards

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

English