

▼ WIDE-ARC PROTRACTOR

DELA.1880.00

- Rule length 400 mm.
- Hardened steel.
- Open protractor for angle readings 10 to 170°.
- Protractor Ø 200 mm.
- Degree graduations.
- Sliding rule with locking screw.

ΔΔ: 420 g.



▼ BASIC BEVEL PROTRACTOR

DELA.1897.02

- Stainless steel, without acute angle attachment.
- Accurate to within 5 minutes of arc.
- Length 300 mm.
- Supplied in a case 370 x 145 x 35 mm.

ΔΔ: 400 g.



▼ PRECISION BEVEL PROTRACTOR

813B.S

- Hardened stainless steel
- Anti-glare matt chrome finish
- Measuring range 0 to 360 °.
- Minimum vernier reading 5 minutes of arc.
- Dimensions 315 x 75 x 20 mm.
- Vernier diameter 70 mm.
- Body graduated in four 90° sectors
- Rotating dial with vernier.
- Dial locking screw.
- 315 mm and 200 mm rules with 45° and 60° bevelled ends.
- 90 mm offset rule for small angles.
- Sliding rule locking screw.
- x10 magnification.
- Cast iron support base.
- Complete with a fitted rigid case 335 x 125 x 47 mm.

ΔΔ: 1.445 kg.



FEELER GAUGES

▼ LONG METRIC FEELER GAUGES

- Rounded tips.

ED	Number of blades	Blade length mm	Blade width mm	Blade thickness in 1/100 mm	ΔΔ g
804.L	19	150	10	4-5-6-7-8-9-10-15-20-25	100
804.SL	19	250	10	30-35-40-50-60-70-80-90-100	210



▼ METRIC FEELER GAUGES

- Blade length 90 mm.

ED	Number of blades	Blade profile	Width x length of blades in mm	Blade thickness in 1/100 mm	ΔΔ g
804	19		10 x 90	4-5-6-7-8-9-10-15-20-25-30	60
804.P	19		10 x 90	35-40-50-60-70-80-90-100	60

