Sentry

Consumer Units and Enclosures

1:4





PRODUCT RANGE Consumer units Surface metal K5504s, K5508s, K5512s, K5516s, K5521s Surface metal, split load K5582s, K5586s, K5566s, K5581s, K5531s Surface insulated K5604s, K5608s, K5612s, K5616s, K5621s Surface insulated, split load K5682s, K5662s, K5632s, K5626s, K5666s, K5686s, K5636s, K5681s, Flush metal K6508s, K6512s, K6516s, K6521s Heating control K5556s, K5656s Stacking kits K6061s, K6062s, K6063s Two module enclosures Surface insulated 5502s RCBO enclosure - metal K5592s Four module enclosures Surface metal 5504s Surface insulated 5604s Weatherproof enclosures Surface insulated, 2 module 5702s Surface insulated, 4 module 5704s Skeleton units For mounting in a mantel/clifton type enclosure 6000s For mounting in a mantel/clifton type enclosure, split load 6001s

Standards and approvals

All Sentry consumer units are designed to fully comply with the requirements of BS EN 60439-3.

IP rating of consumer unit enclosures IP2X.

Description

Sentry consumer units and enclosures are available in various surface metal, surface insulated and flush metal types, designed on a modular basis, with 2 to 21 module enclosures in the range, to accommodate the range of MK modular protection and control products. In addition 24, 32, 42 module surface metal and insulated dual rail comsumer units can be assembled using a suitable stacking kit.

Surface insulated units provides an all insulated housing. Metal units provide a housing with facility for earthing the metal box.

The enclosures are provided with ample wiring space and cable entry points. The lids can be locked with a barrel lock & key (accessory K5593s)

Colours/finishes

All insulated and metal consumer units have a textured magnolia cover and lid. The surface metal consumer unit bases are in magnolia (powder coated paint). The flush bases are of galvanized steel. All 2 and 4 module and Weatherproof enclosures are available in light grey.

Certain models are provided with a preassembled split load arrangement with switch and RCD. The range is complemented by a versatile selection of small, two and four module enclosures suitable for housing RCDs or other combinations of Sentry products. A 2 module enclosure K5592s is suitable for housing the one module RCBO.

All Sentry Consumer Units have neutral and earth terminal bars with 16mm² capacity for solid stranded copper cables.

For enquiries where large number of similarly designed consumer units i.e. specified. MK can provide complete pre-assembled factory built units, subject to certain conditions. For further information please contact the MK Technical Sales Services Department


Features

- Attractive styling
- Modular design
- Suitable for most residential, commercial and light industrial applications
- Fully comply with British and European Harmonised Standards
- Available as an empty enclosure or prefitted with switch disconnector and RCD
- Factory built options available

Consumer Units and Enclosures



2:4



Sentry

Consumer Units and Enclosures

3:4



TECHNICAL SPECIFICATION

Electrical

Maximum current rating:

All Sentry consumer units have a maximum rating of 100A except K5504s, K5604s, which are rated at 63A

Terminal capacity: 16mm² Rated frequency: 50Hz Rated operational voltage: Consumer unit: 220-250V 2 module enclosure: 220-250V

4 module enclosure: 220-415V

Rated insulation voltage Consumer unit: 300V 2 module enclosure: 300V 4 module enclosure: 660V

Short circuit withstand:

16kA rms (based on the use of a BS 1361 Type 2 fuse of rating not exceeding 100A)

Earthing system: Suitable for use with TN-S, TN-C-S and TT systems

Split load

Split load units are supplied with a pre-fitted switch, RCD and suitable cables.

The switch and RCD ratings. The following versions are offered:

	Main	Incomer	RCD
K5682s	100A	Switch	63A
K5662s	100A	Switch	80A
K5632s	100A	T/D RCD	63A
K5666s	100A	Switch	63A
K5686s	100A	Switch	80A
K5636s	100A	T/D RCD	80A
K5681s	100A	Switch	80A
K5631s	100A	T/D RCD	80A
K5626s	100A	T/D RCD	63A
K5582s	100A	Switch	63A
K5566s	100A	Switch	63A
K5586s	100A	Switch	80A
K5581s	100A	Switch	80A
K5531s	100A	T/D RCD	80A


Physical


Ambient operating temperature:

-5°C to +40°C (not to exceed an average of more than 25°C in any 24 hour period)

IP ratings: (see also 'Service Conditions', below)

Consumer unit 2 module enclosure 5502s: IP3X 2 module enclosure 5702s: IP65 2 module enclosure K5592s: IP30 4 module enclosure 5504s: IP3X 4 module enclosure 5604s: IP3X 4 module enclosure 5704s: IP65 Max. installation altitude: 2000 ft





Sentry

Consumer Units and Enclosures

4.4



TECHNICAL SPECIFICATION

Electrical

Maximum current rating:

5702s 2 pole devices up to 100A 5704s 4 pole devices up to 63A

Note:

5702s — Can accept up to 4 module ways with removal of moulded blanks.

5704s – Can accept up to 8 module ways with removal of moulded blanks

Terminal capacity:

5702s: 4 x 6mm² earth and neutral

5704s: 2 x 6mm² and 6 x 4mm² earth and neutral

Rated operational voltage: 220-415V Rated insulation voltage: 660V

Standards

Complies with EN 60670

Installation

Consumer units

The Consumer units are provided with internal busbar shields.

Front covers have lockable lid (using barrel lock & key accessory K5593s), which masks the front cover retaining screw. Removal of the front cover for internal access requires the use of tools.

Cover mounted blanks are provided with each Sentry Consumer unit to fill unused ways.

4,8 and 12 module - 2 off x 1

16 and 21 module - 2 off x 2

If additional unused ways are required the DIN rail mounted blank 5544s must be used to complete the installation.

Two/four module enclosures

Front covers require tools to enable removal and gain internal access.

5604s has provision for tamper-proofing.

Note: Only the K5592s enclosure will accept the one module RCBO's.

Service conditions

Wiring of these products must comply with current IEE regulations.

Consumer units and two and four module enclosures are intended for indoor use in dry conditions and are not suitable for locations where high humidity and/or high temperatures may be experienced.

It is important that during installation of any Sentry enclosure, steps are taken to ensure that the IP rating is maintained, e.g. correct use of cable glands and knockouts/cutouts.

Testing

Site assembled consumer units using MK components comply fully with BS EN 60439-3 so do not require further site testing other than normal routine installation tests.

Split load and multi-incomer arrangements

Such assemblies must utilise the relevant Sentry kit in order to comply with BS EN 60439-3 and to avoid the need for additional testing.

Stacking kits

Accessory kits (stacking frame, fittings and earth cable) can be used to produce stacked dual rail units in the insulated and surface metal ranges for the 12, 16 and 21 module units

K6061s – for 12 module units to create 24 module dual rail consumer unit.

K6062s – for 16 module units to create 32 module dual rail consumer unit.

K6063s – for 21 module units to create 42 module dual rail consumer unit.

Weatherproof enclosures

The weatherproof enclosures may be used for outdoor applications up to the level of the IP65 rating.

The cable entry position on the top and bottom of the enclosure is at the discretion of the installer and can be achieved with suitable tools. Knockouts/cutouts are provided for side entry.

Precautions must be taken to maintain the IP rating, e.g. correct use of cable glands and knockouts. The caps provided must be used to cover the mounting screws.

Note: IP65 rating only achieved with lid in the closed position.

These enclosures will not accept the one module RCBOs.