

LED Rechargeable Hand Lamp HL 1000 A, IP 54, 1000+200 lm

Maximum light output for highest demands.



Product number 1175680
EAN 4007123663422

DESCRIPTION

- With super-bright COB LED at the front.
- Additional switching level for 1 SMD LED in the luminaire head.
- Stepless dimming function 10 % to 100 % for particularly long light duration.
- Rubber coating for increased shock resistance and best grip.
- Bendable base up to +/- 60° with integrated magnet.
- 2 magnets at the back and fold-out hook for flexible use.
- Integrated Li-Ion battery 3.7 V/4.4 Ah with charge indicator.
- USB C charging interface, including USB charging cable.

TECHNICAL DATA

Luminous flux	1000 lm	Number of batteries	1
Total luminous flux secondary source	200 lm	Battery type	Built-in battery pack
Colour temperature	6500 K	Battery technology	Lithium-ion
Colour rendering index	80-89 (class 1B)	Impact strength	IK08
Battery capacity	4.4 Ah	Protection class	III
Battery voltage	3.7 V	Degree of protection (IP)	IP54
Light duration max.	24 h	Colour	anthracite/black
Battery charging time approx.	3.5 h		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.6 kg
Weight of product (without packaging)	0.46 kg	Dimension LxWxH (incl. packing)	12.5 cm x 4.5 cm x 31 cm
Dimension LxWxH (without packing)	4 cm x 6 cm x 26 cm		

SCOPE OF DELIVERY

LED rechargeable hand lamp HL 1000 A, 1m USB C charging cable