



VT-8049 INFRARED MOTION SENSOR-WITH MANUAL OVERRIDE-WHITE (MAX:300W LED)



FEATURES

- Infrared Motion Sensor adopts good sensitivity detector and integrated circuit
- Adjustable Time Delay - Ambient light - Detection distance for versatile scenarios
- Manual override functionality - IR Sensor can be set in Automatic mode or the sensor can be switched on
- High quality receptors for instant functioning
- Effective system for energy saving and safety
- Compatible with V-TAC models

TECHNICAL INFORMATION

Model:	VT-8049
Input Power:	AC:220-240V, 50/60Hz
Unit Color:	White
Body Type:	PC
Dimension:	88x55mm
Operation Temperature:	-25°C to +50°C
Detection Range:	360°
Time Delay:	Min 10sec±3sec, Max 15min±2min
Rated Load:	Max 300W LED
Detection Motion Speed:	0.6-1.5m/s
Ambient Light:	<3-2000LUX(adjustable)
Installation Type:	Surfaced
Detection Angle:	360
Detection Distance:	Max 12m(<24°C)
IP Rating:	IP20
Sensor Type:	Infrared

EMC Certificate: [Check the certificate](#)

LVD Certificate: [Check the certificate](#)

ROHS Certificate: [Check the certificate](#)

IP20
STANDARD

02
YEAR
WARRANTY

LISTING DETAILS

SKU:	1355
Model:	VT-8049
EAN:	3800157624800
Commodity Code:	85365080

PACKAGING

Gross Weight (Kgs):	0.137
Unit CBM:	0.000486
Dimension:	88x55mm

MASTER BOX PACKAGING

Box Qty:	50
Qty Per Pallet:	2000
Length (Box) mm:	90
Width (Box) mm:	90
Height (Box) mm:	60