



SAFETY DATA SHEET

FARECLA G3 PROFESSIONAL SCRATCH REMOVER PASTE

Page: 1

Compilation date: 29/04/2010

Revision date: 06/11/2017

Revision No: 4

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: FARECLA G3 PROFESSIONAL SCRATCH REMOVER PASTE

Product code: 7163

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC31: Polishes and wax blends.

1.3. Details of the supplier of the safety data sheet

Company name: Farecla Products Limited

Broadmeads

Ware

Hertfordshire

SG12 9HS

UK

Tel: +44 (0)1920 465041

Fax: +44 (0)1920 466557

Email: technical@farecla.com

1.4. Emergency telephone number

Emergency tel: +44 (0)1920 465041

8:30 - 16:30 (Monday to Friday)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: -: EUH208

Most important adverse effects: Contains 1,2-benzisothiazolin-3-one. May produce an allergic reaction.

2.2. Label elements

Label elements:

Hazard statements: EUH208: Contains 1,2-benzisothiazolin-3-one. May produce an allergic reaction.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

SAFETY DATA SHEET

FARECLA G3 PROFESSIONAL SCRATCH REMOVER PASTE

Page: 2

Hazardous ingredients:

ALUMINIUM OXIDE - REACH registered number(s): 01-2119529248-35-XXXX

EINECS	CAS	PBT / WEL	CLP Classification	Percent
215-691-6	1344-28-1	Substance with a Community workplace exposure limit.	-	30-50%

HYDROCARBONS, C11-C14, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS - REACH registered number (s): 01-2119456620-43-XXXX

926-141-6	-	-	Asp. Tox. 1: H304; -: EUH066	10-30%
-----------	---	---	------------------------------	--------

WHITE MINERAL OIL (PETROLEUM) - REACH registered number(s): 01-2119487078-27-XXXX

232-455-8	8042-47-5	Substance with a Community workplace exposure limit.	Asp. Tox. 1: H304	1-10%
-----------	-----------	--	-------------------	-------

CALCINED CHINA CLAY

296-473-8	92704-41-1	Substance with a Community workplace exposure limit.	-	1-10%
-----------	------------	--	---	-------

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

[cont...]

SAFETY DATA SHEET

FARECLA G3 PROFESSIONAL SCRATCH REMOVER PASTE

Page: 3

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Wash the spillage site with large amounts of water.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid the formation or spread of dust in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

ALUMINIUM OXIDE

Workplace exposure limits:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	-	-	5mg/m3	-

HYDROCARBONS, C11-C14, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS

EU	1200mg/m3, 165ppm	-	-	-
----	-------------------	---	---	---

WHITE MINERAL OIL (PETROLEUM)

EU	5 mg/m3	-	-	-
----	---------	---	---	---

CALCINED CHINA CLAY

EU	-	-	2.0 mg/m3	-
----	---	---	-----------	---

DNEL/PNEC Values

DNEL / PNEC No data available.

[cont...]

SAFETY DATA SHEET

FARECLA G3 PROFESSIONAL SCRATCH REMOVER PASTE

Page: 4

8.2. Exposure controls

Engineering measures: Not applicable.

Respiratory protection: Respiratory protective device with particle filter.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Environmental: No special requirement.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Paste

Colour: White

Odour: Characteristic odour

Evaporation rate: Negligible

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Miscible in all proportions

Also soluble in: No data available

Viscosity: Viscous

Kinematic viscosity: 25000

Viscosity test method: Brookfield @ 20degC

Boiling point/range °C: Not Available

Flammability limits %: lower: Not Available

Flash point °C: >93

Autoflammability °C: >200

Relative density: 1.45

VOC g/l: 156

Melting point/range °C: Not Available

upper: Not Available

Part.coeff. n-octanol/water: Not Available

Vapour pressure: Not Available

pH: 8.8

9.2. Other information

Other information: Not applicable.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

[cont...]

SAFETY DATA SHEET

FARECLA G3 PROFESSIONAL SCRATCH REMOVER PASTE

Page: 5

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

ALUMINIUM OXIDE

DUST/MIST	RAT	LC50	7.6	mg/l
ORAL	RAT	LD50	> 2000	mg/kg

HYDROCARBONS, C11-C14, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS

DERMAL	RBT	LD50	> 5000	mg/kg
ORAL	RAT	LD50	> 5000	mg/kg
VAPOURS	RAT	8H LC50	> 5000	mg/l

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Delayed / immediate effects: No data available.

Other information: Not applicable.

Section 12: Ecological information

12.1. Toxicity

Hazardous ingredients:

ALUMINIUM OXIDE

Daphnia magna	48H EC50	> 100	mg/l
GREEN ALGA (Selenastrum capricornutum)	48H EC50	> 100	mg/l
Salmo trutta	96H LC50	> 100	mg/l

[cont...]

SAFETY DATA SHEET

FARECLA G3 PROFESSIONAL SCRATCH REMOVER PASTE

Page: 6

HYDROCARBONS, C11-C14, N-ALKANES, ISOALKANES, CYCLICS, < 2% AROMATICS

Daphnia magna	48H EC50	1000	mg/l
Pseudokirchneriella subcapitata	72H ErC50	1000	mg/l
RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	1000	mg/l

CALCINED CHINA CLAY

ALGAE	72H IC50	>100	mg/l
DAPHNIA	48H EC50	>1	mg/l
FISH	96H LC50	>100	mg/l

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: No data available.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Recovery operations: Not applicable.

Waste code number: 08 04 12

Disposal of packaging: Not applicable.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

[cont...]

SAFETY DATA SHEET

FARECLA G3 PROFESSIONAL SCRATCH REMOVER PASTE

Page: 7

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: EUH066: Repeated exposure may cause skin dryness or cracking.
EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.
H304: May be fatal if swallowed and enters airways.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.