

Common mode filters

For high-speed differential signal line, general differential signal line **ALC** series









ALC2012 type













FEATURES

- Obownsized wound type chip common mode filter that maintains required common mode filter characteristics.
- O Differential mode impedance is suppressed, so there is virtually no affect on high speed signals.
- Operating temperature range: -40 to +85°C

APPLICATION

O ETHERNET lines.

PART NUMBER CONSTRUCTION



CHARACTERISTICS SPECIFICATION TABLE

Common mod [at 100MHz]	de impedance	DC resistance [1 line]	Insulation resistance	Rated current	Rated voltage	Part No.
(Ω)min.	(Ω)typ.	(Ω)max.	(M Ω)min.	(mA)max.	(V)max.	
65	90	0.19	10	400	50	ALC2012-900-2P-T00
270	360	0.5	10	220	50	ALC2012-361-2P-T00

Measurement equipment

Measurement item	Product No.	Manufacturer
Common mode impedance	4991A	Keysight Technologies
DC resistance	4338A	Keysight Technologies
Insulation resistance	4339A	Keysight Technologies


^{*} Equivalent measurement equipment may be used.





ALC2012 type

IMPEDANCE VS. FREQUENCY CHARACTERISTICS



Measurement equipment


Product No.	Manufacturer
4991A	Keysight Technologies

^{*} Equivalent measurement equipment may be used.




ALC2012 type

SHAPE & DIMENSIONS




■ PACKAGING STYLE

REEL DIMENSIONS



Dimensions in mm

RECOMMENDED LAND PATTERN




CIRCUIT DIAGRAM

No polarity


Dimensions in mm

TAPE DIMENSIONS




Dimensions in mm

Туре	Α	В	K
ALC2012	(1.4)	(2.25)	(1.4)



Dimensions in mm

■ RECOMMENDED REFLOW PROFILE



□PACKAGE QUANTITY

Package quantity	2000 pcs/reel

■TEMPERATURE RANGE, INDIVIDUAL WEIGHT

Operating temperature range	Storage temperature range*	Individual weight
−40 to +85 °C	−40 to +85 °C	10 mg

^{*} The storage temperature range is for after the assembly.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using this products.

⚠ REMINDERS
The storage period is within 6 months. Be sure to follow the storage conditions (temperature: 5 to 40°C, humidity: 10 to 75% RH or less). If the storage period elapses, the soldering of the terminal electrodes may deteriorate.
Do not use or store in locations where there are conditions such as gas corrosion (salt, acid, alkali, etc.).
Soldering corrections after mounting should be within the range of the conditions determined in the specifications. If overheated, a short circuit, performance deterioration, or lifespan shortening may occur.
When embedding a printed circuit board where a chip is mounted to a set, be sure that residual stress is not given to the chip due to the overall distortion of the printed circuit board and partial distortion such as at screw tightening portions.
Self heating (temperature increase) occurs when the power is turned ON, so the tolerance should be sufficient for the set therma design.
Carefully lay out the coil for the circuit board design of the non-magnetic shield type. A malfunction may occur due to magnetic interference.
Use a wrist band to discharge static electricity in your body through the grounding wire.
On not expose the products to magnets or magnetic fields.
On not use for a nurnose outside of the contents regulated in the delivery specifications

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

If you intend to use the products in the applications listed below or if you have special requirements exceeding the range or conditions set forth in the each catalog, please contact us.

- (1) Aerospace/aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When designing your equipment even for general-purpose applications, you are kindly requested to take into consideration securing protection circuit/device or providing backup circuits in your equipment.