

# Programmable DC Bench Top Power Supply

multicomp<sup>PRO</sup>

RoHS  
Compliant



## Applications

- Military R&D
- Quality Inspection
- Circuit Functional Testing
- Automotive Circuit Testing
- Education and Technical Training
- Electronic component testing and aging experiment
- Monitoring battery charging curve

## Features

- Small body for easy carry
- High resolution: 10mV / 1mA
- List waveform editing output, editable 10 groups of timing output function
- Low ripple / noise
- Over voltage / over current protection
- Output voltage and current curve monitoring function
- Intelligent temperature control fan cooling
- 2.8-inch TFT LCD display
- USB communication interface, support SCPI

## Performance Specifications

Channel	Single Channel Output
Total Output Power	300W
Channel Output	0 - 30V / 0 - 10A
USB Output	5V1A
Display	2.8 inch color LCD display
Dimension	82mm(L) × 142mm(H) × 226mm(D)
Weight	Approx. 1.5kg
Interface	USB
Warranty	03 years

The instrument must be operated continuously for more than 30 minutes at the specified temperature to ensure the following parameters.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

multicomp<sup>PRO</sup>

# Programmable DC Bench Top Power Supply

**multicomp**PRO

Rated Output (0°C-40°C)	Voltage	0 - 30V
	Current	10A
	Power	300W
Load Regulation	Voltage	≤30mV
	Current	≤20mA
Power Regulation	Voltage	≤30mV
	Current	≤20mA
Setting Resolution	Voltage	10mV
	Current	1mA
Readback Resolution	Voltage	10mV
	Current	1mA
Setting Accuracy	Voltage	≤0.1% ± 20mV
	Current	≤0.1% ± 10mA
Readback Accuracy	Voltage	≤0.1% ± 20mV
	Current	≤0.1% ± 10mA
Ripple/Noise(*)	Voltage(Vp-p)	≤30mVp-p
	Voltage (rms)	≤3mVrms
	Current	≤30mA <sub>p-p</sub>
Output temperature coefficient (0°C-40°C)	Voltage	100ppm/°C
	Current	200ppm/°C
Readback temperature coefficient	Voltage	100ppm/°C
	Current	200ppm/°C
Response Time(50%-100% rated load)		≤1.0ms
Storage		4 groups of data
Working Temperature		0°C to 40°C

## Accessories



Power Cord



User Manual



Fuse

## Part Number Table

Description	Part Number
Programmable DC Bench Top Power Supply, 1 channel, 30V, 10A	MP711057

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp**PRO