




Connectors > D-Shaped Connectors > D-Sub Connectors > PCB D-Sub Connectors > D-Sub Shielded Receptacle Assembly: Right Angle, 2.16mm



Connector & Housing Type: **Receptacle**

Connector System: **Cable-to-Board**

Number of Positions: **50**

Centerline (Pitch): **2.16 mm [.085 in]**

Number of Rows: **2**

[All D-Sub Shielded Receptacle Assembly: Right Angle, 2.16mm \(20\)](#)

Features

Mechanical Attachment

	.128 in
PCB Mount Retention	With
PCB Mount Retention Type	Boardlock
Mating Retention	With
Mating Retention Type	Screwlocks
Connector Mounting Type	Panel Mount
Panel Attachment Style	Rear Mount

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	50
Number of Rows	2
PCB Mount Orientation	Right Angle

Housing Features

Centerline (Pitch)	2.16 mm[.085 in]
--------------------	------------------



Housing Material	Polyester GF
------------------	--------------

Dimensions

Row-to-Row Spacing	4.3 mm[.169 in]
PCB Thickness (Recommended)	1.57 mm[.062 in]

Body Features

Connector Profile	Standard
Shield Plating Finish	Bright
Shield Plating Material	Nickel over Copper
Shield Material	Zinc
Primary Product Color	Black

Contact Features

Contact Current Rating (Max)	3.5 A
Contact Mating Area Plating Material Thickness	.76 µm
Contact Options	Installed
Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin

Operation/Application

Circuit Application	Signal
Shielded	Yes

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Termination Features

Rectangular Termination Post & Tail Width	.5 mm[.019 in]
Rectangular Termination Post & Tail Thickness	.25 mm[.01 in]
Termination Method to PCB	Through Hole - Solder

Packaging Features

Packaging Quantity	40
Packaging Method	Tray

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought



TE Part #5100785-1
2MM HDR, 125 POS 9.7MM




TE Part #2057410-1
IMP100S,R,RA2P16C,RG,39



TE Part #2169851-1
Heat Sink Clip, Ganged SFP+



TE Part #5557984-2
RCPT ASSY, 50POS, SHLDED, ACTI



TE Part #5557932-2
RCPT ASSY,SHLD, 50 POSN, RTANG



TE Part #1-644753-6
16P MTA156 HDR ASSY RN STR F/L



TE Part #1883150-2
A600 SZ 2 RCPT F36/blk/59



TE Part #5120791-1
ZP HS3 DB 10R REC 050P CT PD

Documents

CAD Files

Customer View Model

ENG_CVM_CVM_5557932-1_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5557932-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5557932-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English