




Connectors > Audio & Video Connectors > USB Connectors



USB Adapter Type: **A/B**

USB Version: **2.0**

Connector Profile: **Mini**

Connector & Housing Type: **Receptacle**

Number of Ports: **1**

Features

Product Type Features

USB Adapter Type	A/B
USB Version	2.0
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board
USB Connector Type	Mini USB 2.0 Type-AB
Integral Locking Latch	Without

Body Features

Connector Profile	Mini
Shell Plating Material	Nickel
Offset	0 mm

Configuration Features

Number of Ports	1
Number of Positions	5



Mechanical Attachment

PCB Mount Location	Top
PCB Connector Seating	Flush
PCB Mount Retention Type	SMT Hold-Down
Connector Mounting Type	Board Mount
Locking Feature	Without
PCB Mount Alignment Type	Locating Posts

Housing Features

Body Orientation	Right Angle
Centerline (Pitch)	.8 mm[.031 in]
Housing Color	Black
Housing Material	PA 9T

Packaging Features

Packaging Method	Tray
Packaging Quantity	150

Termination Features

Termination Method to PCB	Surface Mount
Termination Post & Tail Length	1.15 mm[.045 in]

Usage Conditions

Soldering Temperature (Max)	260 °C[500 °F]
Mating Cycles (Max)	5000
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]

Contact Features

Contact Current Rating (Max)	1 A
Contact Mating Area Plating Material Thickness	.76 µm[29.92 µin]
Contact Mating Area Plating Material	Gold

Operation/Application

Circuit Application	Power & Signal
Halogen Free	No

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Industry Standards

Industry Standard	USB 2.0
Moisture Sensitivity Level	1
UL Flammability Rating	UL 94V-0

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1734205-1
MINI USB, TYPE B, PLUG. CABLE-KIT

TE Part # 1496476-1
STD USB-A TO MINI-B ASSY, 1M

TE Part # 1929690-1
USB CABLE, USB A to Mini USB,Blue

Customers Also Bought

TE Part #1-826632-7
17P AMPMODU II PIN HDR

TE Part #282837-2
TERMI-BLOK PCB MOUNT 2P

TE Part #5-103168-6
16 MOD II HDR DRST SHRD .100CL

TE Part #292250-8
CT P/HDR BOX H ASSY 8P W/KINK

TE Part #1-207825-1
CPC RCPT ASSEMBLY SIZE 11-4

TE Part #5-103080-2
04 MOD II HDR SRST SHRD .100CL

TE Part #2301996-4
RJ45 JACK INT.MAG. 1GB 1X2

TE Part #1-826629-3
13P AMPMODU II STIFT LEI

TE Part #6-1617039-3
HMS12104S01 = 2100 HMS RELAY

Documents

Product Drawings
Mini USB AB R/A,Rcpt,SMT,TRAY, 0.6mm
English

CAD Files
Customer View Model
ENG_CVM_CVM_1-1734328-1_D.2d_dxf.zip
English
3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1-1734328-1_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-1734328-1_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English