



Relays & Contactors > Circuit Breakers



Circuit Breaker Type: **Magnetic**

Circuit Function: **Series Trip**

Illuminated: **Without**

Actuator Color: **Black**

Operating Voltage: **277 VAC**

Features

Configuration Features

	.75 x 2.065 in
Circuit Function	Series Trip
Number of Poles	1

Product Type Features

Circuit Breaker Type	Magnetic
Illuminated	Without
Illumination Type	No Light
Actuator Type	Toggle

Body Features

Actuator Color	Black
----------------	-------

Electrical Characteristics

Operating Voltage	277 VAC
Current Rating	50 A
Interrupt Capacity	5000A @ 277VAC

Contact Features

Trip Time at 200%	2.2 – 20 seconds
-------------------	------------------

Other

EU RoHS Compliance	Compliant with Exemptions
--------------------	---------------------------



EU ELV Compliance	Compliant
Termination Features	
Terminal Configuration	10-32 Stud
Mechanical Attachment	
Mounting Options	6-32 Mounting Threads
Dimensions	
Product Height	63.5 mm[2.5 in]
Identification Marking	
Stamped Marking Type	International I/O

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Cadmium oxide (7.95% in Component part) <b>Article Safe Usage Statements:</b> Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 8-32589-2  
TERMINAL,PIDG SPD 12-10 10




TE Part # 5-1393254-0  
W91-X152-50=M6/M7/M9/W6/W7



TE Part # 2-36161-3  
TERMINAL,PIDG R IR 12 10

Also in the Series | **Potter & Brumfield W9**



Circuit Breakers(62)

Customers Also Bought



TE Part #2-178128-4  
DYNAMIC 3200 REC HSG 4P SGL Y



TE Part #1-917511-2  
DYNAMIC D-3 REC CONT. 2L AU 0.38 L/P



TE Part #796638-3  
3POS 5.08MM CE R/A HDR,TRM BLK



TE Part #796634-6  
6 POS 5.08MM R/A PLUG,TRM BLK




TE Part #1-796638-0  
10POS 5.08MM CE R/A HDR,TRM BK



TE Part #1393127-9  
PRD-11AG0-120=PRD



TE Part #7-1393246-4  
W23-X1A1G-40=W23/W31



TE Part #4-1393254-3  
W91-X152-15=M6/M7/M9/W6/W7



TE Part #1393255-8  
W93-X112-30=M6/M7/M9/W6/W7



TE Part #3-1618274-6  
HC-3=RELAY, VACUUM, SPDT

Documents

CAD Files

Customer View Model

ENG\_CVM\_CVM\_3-1393254-2\_D.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-1393254-2\_D.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-1393254-2\_D.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

W6/W9 Magnetic Hydraulic Circuit Breaker

English

Agency Approvals

UL

English