# MTL5513 SWITCH/ PROXIMITY DETECTOR **INTERFACE**

two-channel, with line fault detection and phase reversal

The MTL5513 enables two solid-state outputs in the safe area to be controlled by two switches or proximity detectors located in the hazardous area. The Ch1/Ch2 output transistors share a common terminal and can switch +ve or -ve polarity signals. Independent output phase reversal and line fault detection are enabled via switches for each output. LFD indication is provided on the top of the module.

## **SPECIFICATION**

See also common specification

#### **Number of channels**

Two

#### Location of switches

Zone O, IIC, Tó hazardous area Div. 1, Group A hazardous location

## **Location of proximity detectors**

Zone 0, IIC, T4-6 hazardous area if suitably certified Div. 1, Group A hazardous location

## Hazardous-area inputs

Inputs conforming to BS EN60947-5-6:2001 standards for proximity detectors (NAMUR)

## Voltage applied to sensor

7 to 9V dc from  $1k\Omega \pm 10\%$ 

## Input/output characteristics

Normal phase

Outputs closed if input > 2.1mA (<  $2\text{k}\Omega$  in input circuit) Outputs open if input < 1.2mA (>  $10\text{k}\Omega$  in input circuit) Hysteresis:  $200\mu A$  (650 $\Omega$ ) nominal

## Line fault detection (LFD) (when selected)

User-selectable for each channel via switches on the side of the unit. Line faults are indicated by an LED for each channel.

Open-circuit alarm on if lin < 50µA Open-circuit alarm off if lin > 250µA

Short-circuit alarm on if Rin  $< 100\Omega$ 

Short-circuit alarm off if Rin >  $360\Omega$ 

Note: Resistors must be fitted when using the LFD facility with a contact input  $500\Omega$  to  $1k\Omega$  in series with switch

 $20k\Omega$  to  $25k\Omega$  in parallel with switch


## Phase reversal

Independent for each channel, user-selectable

### Safe-area outputs

Floating solid-state outputs compatible with logic circuits

Operating frequency: dc to 500Hz Max. off-state voltage: ± 35V Max. off-state leakage current:  $\pm 50 \mu A$ Max. on-state resistance:  $25\Omega$ Max. on-state current:  $\pm 50mA$ 



Terminal	Function
1	Input -ve (Ch 1)
2	Input +ve (Ch 1)
3	To earth leakage detector*
4	Input –ve (Ch 2)
5	Input +ve (Ch 2)
6	To earth leakage detector*
10	Output (Ch 2)
11	Output (Ch 1/Ch 2)
12	Output (Ch 1)
13	Supply –ve

\* Signal plug HAZ1-3 is required for access to this function

#### **LED** indicators

Green: power indication

Yellow: two: channel status, on when outputs are on Red: two: LFD indication, on when line fault detected

## **Maximum current consumption**

27mA at 24V

## Power dissipation within unit

0.65W typical at 24V, with 10mA loads 0.78W max. with 50mA loads

## Safety description (each channel)

 $V_0 = 10.5V$   $I_0 = 14 \text{ mA}$   $P_0 = 37 \text{ mW}$   $U_m = 253 \text{ V}$  rms or dc

The given data is only intended as a product description and should not be regarded as a legal warranty of properties or guarantee. In the interest of further technical developments, we reserve the right to make design changes.

# **MTL5500 SERIES COMMON SPECIFICATION**

Please go to our website at www.mtl-inst.com for the latest information regarding safety approvals, certificates and entity parameters.

#### **Connectors**

Each MTL5500 unit is supplied with signal connectors, as applicable.

When using crimp ferrules for the hazardous and nonhazardous (safe) signal connectors the metal tube length should be 12mm and the wire trim length 14mm.

## Isolation

250V rms, tested at 2200V rms minimum, between safe-area, hazardous-area and power supply terminals

50V ac or dc between safe-area circuits where applicable.

## Supply voltage

20 - 35V dc

#### Location of units

Safe area

#### **Terminals**

Accepts conductors of up to 2.5mm<sup>2</sup> stranded or single-core

## Mounting

MTL5500 series backplanes

#### Ambient temperature limits

-20 to +60°C (-6 to +140°F) operating  $-40 \text{ to } +80^{\circ}\text{C} \text{ (}-40 \text{ to } +176^{\circ}\text{F)} \text{ storage}$ 

## **Humidity**

5 to 95% relative humidity

## Weight


110g approximately (except where indicated)

HART® is a registered trademark of HART Communication Foundation

## **DIMENSIONS (mm)**

Optional TH5000 tag holder for individual isolator identification. Accepts tag label 25 x 12.5  $\pm$ 0.5mm, 0.2mm thick





The given data is only intended as a product description and should not be regarded as a legal warranty of properties or guarantee. In the interest of further technical developments, we reserve the right to make design changes.