SAFETY DATA SHEET



This safety data sheet was created pursuant to the requirements of: Safety data sheet according to Regulation (EC) 2020/878

Revision date 12/12/2023 **Revision Number** 3.23

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product Name Platenclene

Product Code(s) APCL100, ZA

00191 Safety data sheet number

Unique Formula Identifier (UFI) QDH0-00HA-C00D-ESY8

Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Cleaning agent

Uses advised against No specific uses advised against are identified

FRANCE

info@af-net.com

1.3. Details of the supplier of the safety data sheet

Manufacturer Supplier

HK WENTWORTH LIMITED AF INTERNATIONAL MacDermid Alpha Electronics Solutions 32 RUE DE TOURNENFILS 91540 MENNECY

ASHBY PARK COALFIELD WAY ASHBY de la ZOUCH

LEICESTERSHIRE. LE65 1JR

+33 (0) 1 82 88 47 94

UNITED KINGDOM

+44 (0) 1530 419600 +44 (0) 1530 416640

info@af-net.com

For further information, please contact

info@af-net.com E-mail address

1.4. Emergency telephone number

POISON INFORMATION CENTRE (Beaumont Hospital, Republic of Ireland only) +353 (0)1 **Emergency Telephone**

809 2166 (08:00 - 22:00)

Emergency Telephone - IN CASE OF EMERGENCY CALL: +44 1865 407333 (24hr, Provided by Carechem 24)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to

Regulation (EC) No. 1272/2008 [CLP]

Aspiration hazard Category 1 - (H304)

2.2. Label elements

Contains hydrocarbons, C11-C12, isoalkanes, <2% aromatics, Hydrocarbons, C11-C13, isoalkanes, <2% aromatics



Signal word Danger

Hazard statements

H304 - May be fatal if swallowed and enters airways

Precautionary Statements - EU (§28, 1272/2008)

P102 - Keep out of reach of children.

P301 + P310 - IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

P331 - Do NOT induce vomiting.

P501 - Dispose of contents/container in accordance with local, regional, national, and international regulations as applicable.

2.3. Other hazards

This mixture contains no substance considered to be persistent, bioaccumulating or toxic (PBT). This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB).

Endocrine Disruptor Information This product does not contain any known or suspected endocrine disruptors.

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable

3.2 Mixtures

	Chemical name	Weight-%	REACH registration	EC No (EU	Classification according	Specific	M-Factor	M-Factor
l			number	Index No)	to Regulation (EC) No.	concentration		(long-term)

Revision	date	12/12/2023

				1272/2008 [CLP]	limit (SCL)		
Hydrocarbons, C11-C13, isoalkanes, <2% aromatics	30-60	01-2119456810-40-00 00	920-901-0	Asp. Tox. 1 (H304)	-	-	-
hydrocarbons, C11-C12, isoalkanes, <2% aromatics	30-60	01-2119472146-39-00 00	918-167-1	Asp. Tox. 1 (H304) Flam. Liq. 3 (H226)	-	-	-

Full text of H- and EUH-phrases: see section 16

Acute Toxicity Estimate

This product does not contain candidate substances of very high concern at a concentration >=0.1% (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice Immediate medical attention is required. Show this safety data sheet to the doctor in

attendance.

Inhalation Aspiration into lungs can produce severe lung damage. If breathing has stopped, give

artificial respiration. Get medical attention immediately. Remove to fresh air. Avoid direct contact with skin. Use barrier to give mouth-to-mouth resuscitation. If breathing is difficult, (trained personnel should) give oxygen. Get immediate medical attention. Delayed

pulmonary edema may occur.

Eye contact Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Keep

eye wide open while rinsing. Do not rub affected area.

Skin contact Wash off immediately with soap and plenty of water while removing all contaminated clothes

and shoes.

Ingestion ASPIRATION HAZARD IF SWALLOWED - CAN ENTER LUNGS AND CAUSE DAMAGE.

Do NOT induce vomiting. If vomiting occurs spontaneously, keep head below hips to prevent aspiration. Rinse mouth. Never give anything by mouth to an unconscious person.

Get immediate medical attention.

Self-protection of the first aider Remove all sources of ignition. Ensure that medical personnel are aware of the material(s)

involved, take precautions to protect themselves and prevent spread of contamination. Use personal protective equipment as required. See section 8 for more information. Avoid direct

contact with skin. Use barrier to give mouth-to-mouth resuscitation.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms Difficulty in breathing. Coughing and/ or wheezing. Dizziness.

Effects of Exposure None.

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors Because of the danger of aspiration, emesis or gastric lavage should not be used unless the

risk is justified by the presence of additional toxic substances.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable Extinguishing Media Dry chemical. Carbon dioxide (CO2). Water spray. Alcohol resistant foam.

Large Fire CAUTION: Use of water spray when fighting fire may be inefficient.

Unsuitable extinguishing mediaDo not scatter spilled material with high pressure water streams.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the

chemical

Risk of ignition. Keep product and empty container away from heat and sources of ignition. In the event of fire, cool tanks with water spray. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.

5.3. Advice for firefighters

Special protective equipment and precautions for fire-fighters

Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Evacuate personnel to safe areas. Use personal protective equipment as required. See

section 8 for more information. Avoid contact with skin, eyes or clothing. Ensure adequate ventilation. Keep people away from and upwind of spill/leak. ELIMINATE all ignition sources (no smoking, flares, sparks or flames in immediate area). Pay attention to flashback. Take precautionary measures against static discharges. All equipment used when handling the

product must be grounded. Do not touch or walk through spilled material.

Other information Ventilate the area. Refer to protective measures listed in Sections 7 and 8.

For emergency responders Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions Refer to protective measures listed in Sections 7 and 8. Prevent further leakage or spillage if

safe to do so. Prevent product from entering drains.

6.3. Methods and material for containment and cleaning up

Methods for containment Stop leak if you can do it without risk. Do not touch or walk through spilled material. A

vapour suppressing foam may be used to reduce vapours. Dyke far ahead of spill to collect run-off water. Keep out of drains, sewers, ditches and waterways. Absorb with earth, sand

or other non-combustible material and transfer to containers for later disposal.

Methods for cleaning up Take precautionary measures against static discharges. Dam up. Soak up with inert

absorbent material. Pick up and transfer to properly labelled containers.

Prevention of secondary hazards Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Reference to other sectionsSee section 8 for more information. See section 13 for more information.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

vapours or mists. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Use grounding and bonding connection when transferring this material to prevent static discharge, fire or explosion. Use with local exhaust ventilation. Use spark-proof tools and explosion-proof equipment. Keep in an area equipped with sprinklers.

Revision date 12/12/2023

Use according to package label instructions.

General hygiene considerations Do not eat, drink or smoke when using this product. Contaminated work clothing should not

be allowed out of the workplace. Regular cleaning of equipment, work area and clothing is recommended. Wash hands before breaks and immediately after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place. Keep away from heat,

sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity). Keep in properly labelled containers. Do not store near combustible materials. Keep in an area equipped with sprinklers. Store in accordance with the particular national regulations. Store in accordance with local regulations. Store locked up. Keep out of the

reach of children. Store away from other materials.

Storage class (TRGS 510) LGK 3.

7.3. Specific end use(s)

Risk Management Methods (RMM) The information required is contained in this Safety Data Sheet.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure Limits This product, as supplied, does not contain any hazardous materials with occupational

exposure limits established by the region specific regulatory bodies.

Biological occupational exposure

limits

This product, as supplied, does not contain any hazardous materials with biological limits

established by the region specific regulatory bodies.

Derived No Effect Level (DNEL) - Workers

	Chemical name	Oral	Dermal	Inhalation
1	-(2-Butoxy-1-methylethoxy)propan-2-	-	134 mg/kg bw/day [4] [6]	189 mg/m³ [4] [6]
	ol			
	29911-28-2			

[4] Systemic health effects.

[6] Long term.

Derived No Effect Level (DNEL) - General Public

Chemical name	Oral	Dermal	Inhalation
1-(2-Butoxy-1-methylethoxy)propan-2-	16 mg/kg bw/day [4] [6]	-	56 mg/m³ [4] [6]
ol			-
29911-28-2			

[4] Systemic health effects.

[6] Long term.

Predicted No Effect Concentration (PNEC)

Chemical name	Freshwater	Freshwater	Marine water	Marine water	Air
		(intermittent release)		(intermittent release)	
1-(2-Butoxy-1-methylethox y)propan-2-ol 29911-28-2	0.519 mg/L	5.19 mg/L	0.0519 mg/L	-	-

Chemical name	Freshwater sediment	Marine sediment	Sewage treatment	Soil	Food chain
1-(2-Butoxy-1-methylethox y)propan-2-ol 29911-28-2	2.96 mg/kg sediment dw	0.296 mg/kg sediment dw	100 mg/L	0.287 mg/kg soil dw	-

8.2. Exposure controls

Engineering controls Ensure adequate ventilation, especially in confined areas.

Personal protective equipment

Eye/face protection Tight sealing safety goggles.

Hand protection Wear suitable gloves. Impervious gloves.

Skin and body protection Wear suitable protective clothing. Long sleeved clothing. Chemical resistant apron.

Antistatic boots.

Respiratory protection No protective equipment is needed under normal use conditions. If exposure limits are

exceeded or irritation is experienced, ventilation and evacuation may be required.

General hygiene considerations Do not eat, drink or smoke when using this product. Contaminated work clothing should not

be allowed out of the workplace. Regular cleaning of equipment, work area and clothing is recommended. Wash hands before breaks and immediately after handling the product.

Environmental exposure controls No information available.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical stateLiquidAppearanceLiquid

ColourColourlessOdourCharacteristic.

Odour threshold No information available

<u>Property</u> <u>Values</u> <u>Remarks • Method</u>

Melting point / freezing pointNo data availableNone knownInitial boiling point and boiling rangeNo data availableNone knownFlammabilityNo data availableNone knownFlammability Limit in AirNone known

Upper flammability or explosive No data available

limits

Lower flammability or explosive No data available

limits

Flash point > 61 °C Closed cup
Autoignition temperature No data available None known
Decomposition temperature None known

Decomposition temperaturepH

None known
pH (concentrated solution): 5-7

pH (as aqueous solution) No data available None known Kinematic viscosity No data available None known Dynamic viscosity 1.48 mPa s @ 25°C None known Water solubility No data available None known Solubility(ies) No data available None known **Partition coefficient** No data available None known No data available Vapour pressure None known Relative density No data available None known

Bulk density
No data available
No data available

Relative vapour density No data available None known

Particle characteristics

Particle Size No information available Particle Size Distribution No information available

9.2. Other information

9.2.1. Information with regards to physical hazard classes

Explosive properties Not considered to be explosive.

Oxidising properties Does not meet the criteria for classification as oxidizing.

9.2.2. Other safety characteristics No information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity No information available.

10.2. Chemical stability

Stability Stable under normal conditions.

Explosion data

Sensitivity to mechanical impact None. Sensitivity to static discharge Yes.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

Page 7/13

10.4. Conditions to avoid

Conditions to avoid Heat, flames and sparks.

10.5. Incompatible materials

Incompatible materialsNone known based on information supplied.

10.6. Hazardous decomposition products

Hazardous decomposition products None known based on information supplied.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Information on likely routes of exposure

Product Information

Inhalation Specific test data for the substance or mixture is not available. Aspiration into lungs can

produce severe lung damage. May cause pulmonary edema. Pulmonary edema can be

fatal. May cause irritation of respiratory tract.

Eye contact Specific test data for the substance or mixture is not available. May cause irritation.

Skin contact Repeated exposure may cause skin dryness or cracking.

Ingestion Specific test data for the substance or mixture is not available. Potential for aspiration if

swallowed. May cause lung damage if swallowed. Aspiration may cause pulmonary edema

and pneumonitis. May be fatal if swallowed and enters airways.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms Difficulty in breathing. Coughing and/ or wheezing. Dizziness.

Acute toxicity

Numerical measures of toxicity

The following values are calculated based on chapter 3.1 of the GHS document

 ATEmix (oral)
 99,999.000 mg/kg

 ATEmix (dermal)
 99,999.00 mg/kg

 ATEmix (inhalation-gas)
 99,999.00 ppm

 ATEmix (inhalation-vapour)
 99,999.00 mg/l

 ATEmix (inhalation-dust/mist)
 99,999.00 mg/l

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation Based on available data, the classification criteria are not met.

Serious eye damage/eye irritation Based on available data, the classification criteria are not met.

Respiratory or skin sensitisation Based on available data, the classification criteria are not met.

Germ cell mutagenicity Based on available data, the classification criteria are not met.

Carcinogenicity Based on available data, the classification criteria are not met.

Reproductive toxicityBased on available data, the classification criteria are not met.

STOT - single exposure Based on available data, the classification criteria are not met.

STOT - repeated exposureBased on available data, the classification criteria are not met.

Aspiration hazard May be fatal if swallowed and enters airways.

11.2. Information on other hazards

11.2.1. Endocrine disrupting properties

Endocrine disrupting properties The substance/mixture does not contain components considered to have endocrine

disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

(EO) 2017/2100 of Continues and Regulation (EO) 2010/000 at levels of 0.1 % of high

11.2.2. Other information

Other adverse effects No information available.

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity

12.2. Persistence and degradability

Persistence and degradability No information available.

12.3. Bioaccumulative potential

Bioaccumulation There is no data for this product.

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment The product does not contain any substance(s) classified as PBT or vPvB above the

threshold of declaration.

12.6. Endocrine disrupting properties

Endocrine disrupting properties

The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

12.7. Other adverse effects

No information available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste from residues/unused products

Should not be released into the environment. Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.

Contaminated packaging

Empty containers pose a potential fire and explosion hazard. Do not cut, puncture or weld containers.

SECTION 14: Transport information

A -	

14.1	UN number or ID number	Not regulated
14.2	UN proper shipping name	Not regulated
14.3	Transport hazard class(es)	Not regulated
14.4	Packing group	Not regulated
	Environmental hazards	Not applicable

14.6 Special precautions for user

Special Provisions None

IMDG

14.1	UN number or ID number	Not regulated
14.2	UN proper shipping name	Not regulated
14.3	Transport hazard class(es)	Not regulated
14.4	Packing group	Not regulated
	Environmental hazards	Not applicable
		• •

14.6 Special precautions for user **Special Provisions**

14.7 Maritime transport in bulk No information available according to IMO instruments

RID

14.1	UN number or ID number	Not regulated
14.2	UN proper shipping name	Not regulated
14.3	Transport hazard class(es)	Not regulated
14.4	Packing group	Not regulated
14.5	Environmental hazards	Not applicable

14.6 Special precautions for user **Special Provisions**

None

ADR

	_	
14.1	UN number or ID number	Not regulated
14.2	UN proper shipping name	Not regulated
14.3	Transport hazard class(es)	Not regulated
14.4	Packing group	Not regulated
14.5	Environmental hazards	Not applicable

14.6 Special precautions for user

Special Provisions None

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations

Germany

Water hazard class (WGK) slightly hazardous to water (WGK 1)

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Authorisations and/or restrictions on use:

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV) This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII)

Persistent Organic Pollutants

Not applicable

Dangerous substance category per Seveso Directive (2012/18/EU)

P5a - FLAMMABLE LIQUIDS P5b - FLAMMABLE LIQUIDS P5c - FLAMMABLE LIQUIDS

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

International Inventories

TSCA Contact supplier for inventory compliance status **DSL/NDSL** Contact supplier for inventory compliance status **EINECS/ELINCS** Contact supplier for inventory compliance status **ENCS** Contact supplier for inventory compliance status **IECSC** Contact supplier for inventory compliance status Contact supplier for inventory compliance status **KECL PICCS** Contact supplier for inventory compliance status AIIC Contact supplier for inventory compliance status **NZIoC** Contact supplier for inventory compliance status

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances

ENCS - Japan Existing and New Chemical Substances

IECSC - China Inventory of Existing Chemical Substances

KECL - Korean Existing and Evaluated Chemical Substances

PICCS - Philippines Inventory of Chemicals and Chemical Substances

AIIC - Australian Inventory of Industrial Chemicals

NZIoC - New Zealand Inventory of Chemicals

15.2. Chemical safety assessment

Chemical Safety Report No information available

SECTION 16: Other information

Key or legend to abbreviations and acronyms used in the safety data sheet

Full text of H-Statements referred to under section 3

H226 - Flammable liquid and vapour

H304 - May be fatal if swallowed and enters airways

Legend

SVHC: Substances of Very High Concern for Authorisation:

Legend Section 8: Exposure controls/personal protection

TWA TWA (time-weighted average) STEL STEL (Short Term Exposure Limit)

Ceiling Maximum limit value Sk* Skin designation

+ Sensitisers

Classification procedure			
Classification according to Regulation (EC) No. 1272/2008 [CLP]	Method Used		
Acute oral toxicity	Calculation method		
Acute dermal toxicity	Calculation method		
Acute inhalation toxicity - gas	Calculation method		
Acute inhalation toxicity - vapour	Calculation method		
Acute inhalation toxicity - dust/mist	Calculation method		
Skin corrosion/irritation	Calculation method		
Serious eye damage/eye irritation	Calculation method		
Respiratory sensitisation	Calculation method		
Skin sensitisation	Calculation method		
Mutagenicity	Calculation method		
Carcinogenicity	Calculation method		
Reproductive toxicity	Calculation method		
STOT - single exposure	Calculation method		
STOT - repeated exposure	Calculation method		
Acute aquatic toxicity	Calculation method		
Chronic aquatic toxicity	Calculation method		
Aspiration hazard	Calculation method		
Ozone	Calculation method		

Key literature references and sources for data used to compile the SDS

Agency for Toxic Substances and Disease Registry (ATSDR)

U.S. Environmental Protection Agency ChemView Database

European Food Safety Authority (EFSA)

European Chemicals Agency (ECHA) Committee for Risk Assessment (ECHA_RAC)

European Chemicals Agency (ECHA) (ECHA_API)

EPA (Environmental Protection Agency)

Acute Exposure Guideline Level(s) (AEGL(s))

U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act

U.S. Environmental Protection Agency High Production Volume Chemicals

Food Research Journal

Hazardous Substance Database

International Uniform Chemical Information Database (IUCLID)

National Institute of Technology and Evaluation (NITE)

Australian National Industrial Chemicals Notification and Assessment Scheme (NICNAS)

NIOSH (National Institute for Occupational Safety and Health)

National Library of Medicine's ChemID Plus (NLM CIP)

National Library of Medicine's PubMed database (NLM PUBMED)

National Toxicology Program (NTP)

New Zealand's Chemical Classification and Information Database (CCID)

Organisation for Economic Co-operation and Development Environment, Health, and Safety Publications

Organisation for Economic Co-operation and Development High Production Volume Chemicals Programme

Organisation for Economic Co-operation and Development Screening Information Data Set

World Health Organization

Revision date

12/12/2023

Safety Data Sheet according to Regulation (EC) No. 1907/2006 (REACH)

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet