

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Relevant identified uses

No additional information available

1.2. Details of the supplier of the safety data sheet

Premier Farnell
150 Armley Road
Leeds LS12 2QQ
Tel. : +44 (0) 8701 202530

Emergency telephone number

+44 1865 407333

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Serious eye damage/eye irritation,
Category 2 : H319

Skin sensitisation, Category 1 : H317

Full text of H- and EUH-statements: see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)



GHS07

Signal word (CLP)

: Warning

Contains

: 2-Methyl-2-propenoic acid monoester with 1,2-propanediol, Acetic acid
2-phenylhydrazide

Hazard statements (CLP)

: H317 - May cause an allergic skin reaction.
H319 - Causes serious eye irritation.

Precautionary statements (CLP)

: P261 - Avoid breathing vapours.
P280 - Wear protective clothing, eye protection, face protection.
P321 - Specific treatment (see supplemental first aid instruction on this label).
P333+P313 - If skin irritation or rash occurs: Get medical advice/attention.
P337+P313 - If eye irritation persists: Get medical advice/attention.
P362+P364 - Take off contaminated clothing and wash it before reuse.

2.3. Other hazards

PBT: not relevant – no registration required

vPvB: not relevant – no registration required

Contains no PBT/vPvB substances $\geq 0.1\%$ assessed in accordance with REACH Annex XIII

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
2-Methyl-2-propenoic acid monoester with 1,2-propanediol	CAS-No.: 27813-02-1 EC-No.: 248-666-3 REACH-no: 01-2119490226-37	≥10 – <20	Eye Irrit. 2, H319 Skin Sens. 1B, H317
Amorphous Silica substance with national workplace exposure limit(s) (AT, CZ, DE, EE, LV, SI, MK)	CAS-No.: 7631-86-9 EC-No.: 231-545-4 REACH-no: 01-2119379499-16	≥5 – <10	Not classified
α, α-dimethylbenzyl hydroperoxide substance with national workplace exposure limit(s) (LT, LV)	CAS-No.: 80-15-9 EC-No.: 201-254-7 EC Index-No.: 617-002-00-8 REACH-no: 01-2119475796-19	≥0.5 – <1	Org. Perox. E, H242 Acute Tox. 4 (Oral), H302 (ATE=500 mg/kg bodyweight) Acute Tox. 4 (Dermal), H312 (ATE=1100 mg/kg bodyweight) Acute Tox. 3 (Inhalation), H331 Skin Corr. 1B, H314 STOT RE 2, H373 Aquatic Chronic 2, H411
Acetic acid 2-phenylhydrazide	CAS-No.: 114-83-0	< 0.5	Acute Tox. 3 (Oral), H301 (ATE=270 mg/kg body weight) Skin Irrit. 2, H315 Eye Irrit. 2, H319 Skin Sens. 1, H317 STOT SE 3, H335
maleic acid	CAS-No.: 110-16-7 EC-No.: 203-742-5 EC Index-No.: 607-095-00-3	< 0.5	Acute Tox. 3 (Oral), H301 (ATE=270 mg/kg bodyweight) Skin Irrit. 2, H315 Eye Irrit. 2, H319 Skin Sens. 1, H317 STOT SE 3, H335

Specific concentration limits:		
Name	Product identifier	Specific concentration limits
α, α-dimethylbenzyl hydroperoxide	CAS-No.: 80-15-9 EC-No.: 201-254-7 EC Index-No.: 617-002-00-8 REACH-no: 01-2119475796-19	(1 ≤C < 3) Eye Irrit. 2, H319 (1 <C < 10) STOT SE 3, H335 (3 ≤C < 10) Skin Irrit. 2, H315 (3 ≤C < 10) Eye Dam. 1, H318 (10 ≤C ≤ 100) Skin Corr. 1B, H314

Full text of H- and EUH-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: Move the affected person away from the contaminated area and into the fresh air. If you feel unwell, seek medical advice.
First-aid measures after skin contact	: Wash skin with plenty of water. Get medical advice/attention.
First-aid measures after eye contact	: Rinse immediately with plenty of water. Rinse cautiously with water for several minutes. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Rinse mouth out with water. Drink plenty of water. Do not induce vomiting.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after eye contact : redness, itching, tears.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Carbon dioxide. Foam. Water spray. Dry powder.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Carbon dioxide. Carbon monoxide.

5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers.

Protection during firefighting : Use self-contained breathing apparatus and chemically protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Avoid contact with skin and eyes.

6.1.1. For non-emergency personnel

Emergency procedures : Avoid contact with skin and eyes.

6.1.2. For emergency responders

No additional information available

6.2. Environmental precautions

Avoid release to the environment. Do not allow to enter drains or water courses.

6.3. Methods and material for containment and cleaning up

For containment : Collect spillage. Absorb spilled material with sand or earth.

Methods for cleaning up : Clean up any spills as soon as possible, using an absorbent material to collect it. This material and its container must be disposed of in a safe way, and as per local legislation.

6.4. Reference to other sections

See Section 8. For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Avoid contact with eyes. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Do not eat, drink or smoke when using this product. Provide local exhaust or general room ventilation.

Hygiene measures : Take off immediately all contaminated clothing and wash it before reuse. Do not eat, drink or smoke when using this product. Wear personal protective equipment.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a closed container. Store in a well-ventilated place.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

Personal protective equipment:

Gloves. Safety glasses.

Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection : Safety glasses (EN 166). Protective goggles (EN 166)

8.2.2.2. Skin protection

Hand protection : Gloves

8.2.2.3. Respiratory protection

Respiratory protection : In case of insufficient ventilation, wear suitable respiratory equipment

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls : Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Liquid

Colour : Orange.

Odour : Mild.

Odour threshold : Not available

Melting point : Not available

Freezing point : Not available

Boiling point : Not available

Flammability : Not available

Explosive properties : Not available

Oxidising properties	: Not available.
Explosive limits	: Not available
Lower explosion limit	: Not available
Upper explosion limit	: Not available
Flash point	: >93°C
Auto-ignition temperature	: Not available
Decomposition temperature	: Not available
pH	: Not applicable
Viscosity, kinematic	: Not available
Viscosity, dynamic	: 30000 – 50000 cP
Solubility	: Insoluble in water
Partition coefficient n-octanol/water (Log Kow)	: Not available
Vapour pressure	: Not available
Vapour pressure at 50°C	: Not available
Density	: Not available
Relative density	: Not available
Relative vapour density at 20°C	: Not applicable.
Particle characteristics	: Not applicable

9.2. Other information

9.2.1. Information with regard to physical hazard classes

No additional information available

9.2.2. Other safety characteristics

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Stable under normal conditions of use. Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

Strong acids.

10.6. Hazardous decomposition products

Carbon dioxide. Carbon monoxide. May liberate toxic gases.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral) : Not classified

Acute toxicity (dermal) : Not classified

Acute toxicity (inhalation) : Not classified

Safety Data Sheet

multicompPRO

2-Methyl-2-propenoic acid monoester with 1,2-propanediol (27813-02-1)	
LD50 oral rat	≥ 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 401 (Acute Oral Toxicity)
LD50 dermal rabbit	> 5000 mg/kg bodyweight Animal: rabbit, Animal sex: male
Acetic acid 2-phenylhydrazide (114-83-0)	
LD50 oral rat	270 mg/kg Source: THOMSON
Amorphous Silica (7631-86-9)	
LD50 oral rat	3160 mg/kg Source: TOMES; HAZARDTEXT
LD50 dermal rabbit	> 5000 mg/kg Source: ECHA
LC50 Inhalation - Rat (Dust/Mist)	5.01 mg/l Source: ECHA
α, α-dimethylbenzyl hydroperoxide (80-15-9)	
LC50 Inhalation - Rat [ppm]	220 ppm Animal: rat, Animal sex: male, Remarks on results: other:
Skin corrosion/irritation	Not classified pH: Not applicable
Amorphous Silica (7631-86-9)	
pH	3.5 – 4.4
Serious eye damage/irritation	Causes serious eye irritation. pH: Not available
Amorphous Silica (7631-86-9)	
pH	3.5 – 4.4
Respiratory or skin sensitisation	May cause an allergic skin reaction.
Germ cell mutagenicity	Not classified
Carcinogenicity	Not classified
Amorphous Silica (7631-86-9)	
IARC group	3 - Not classifiable
Reproductive toxicity	Not classified
STOT-single exposure)	Not classified
Acetic acid 2-phenylhydrazide (114-83-0)	
STOT-single exposure	May cause respiratory irritation.
STOT-repeated exposure	Not classified
2-Methyl-2-propenoic acid monoester with 1,2-propanediol (27813-02-1)	
LOAEC (inhalation, rat, gas, 90 days)	350 ppm Animal: rat, Guideline: OECD Guideline 413 (Subchronic Inhalation Toxicity: 90-Day Study), Remarks on results: other:
NOAEL (oral, rat, 90 days)	300 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)
NOAEC (inhalation, rat, gas, 90 days)	100 ppm Animal: rat, Guideline: OECD Guideline 413 (Subchronic Inhalation Toxicity: 90-Day Study), Remarks on results: other:
α, α-dimethylbenzyl hydroperoxide (80-15-9)	
STOT-repeated exposure	May cause damage to organs through prolonged or repeated exposure.

Aspiration hazard : Not classified

11.2. Information on other hazards

No additional information available

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

SECTION 12: Ecological information

12.1. Toxicity

Hazardous to the aquatic environment, short-term (acute) : Not classified
 Hazardous to the aquatic environment, long-term (chronic) : Not classified.
 Not rapidly degradable
 Additional information : No data available.

2-Methyl-2-propenoic acid monoester with 1,2-propanediol (27813-02-1)	
LC50 - Fish [1]	233.174 mg/l Source: ECOSAR
EC50 - Crustacea [1]	> 143 mg/l Test organisms (species): Daphnia magna
EC50 72h - Algae [1]	> 97.2 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
NOEC (chronic)	45.2 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
Acetic acid 2-phenylhydrazide (114-83-0)	
LC50 - Fish [1]	2.101 mg/l Source: ECOSAR
EC50 96h - Algae [1]	0.852 mg/l Source: ECOSAR
Amorphous Silica (7631-86-9)	
LC50 - Fish [1]	10000 mg/l Source: ECHA
EC50 - Crustacea [1]	> 5000 mg/l Source: ECHA
EC50 72h - Algae [1]	> 173.1 mg/l Source: ECHA

12.2. Persistence and degradability

Persistence and degradability : Biodegradability in water: no data available.

12.3. Bioaccumulative potential

Bioaccumulative potential : No bioaccumulation data available.

2-Methyl-2-propenoic acid monoester with 1,2-propanediol (27813-02-1)

Partition coefficient n-octanol/water (Log Pow) : 0.48

Acetic acid 2-phenylhydrazide (114-83-0)

Partition coefficient n-octanol/water (Log Pow) : 0.7

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

PBT: not relevant – no registration required
 vPvB: not relevant – no registration required

12.6. Endocrine disrupting properties

No additional information available

12.7. Other adverse effects

Additional information : No other effects known

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 sg.element14.com/b/multicomp-pro

Regional legislation (waste)	: Disposal must be done according to official regulations.
Product/Packaging disposal recommendations	: Avoid release to the environment.
HP Code	: HP3 - "Flammable:" – flammable liquid waste: liquid waste having a flash point below 60 °C or waste gas oil, diesel and light heating oils having a flash point > 55°C and ≤ 75°C; – flammable pyrophoric liquid and solid waste: solid or liquid waste which, even in small quantities, is liable to ignite within five minutes after coming into contact with air; – flammable solid waste: solid waste which is readily combustible or may cause or contribute to fire through friction; – flammable gaseous waste: gaseous waste which is flammable in air at 20 °C and a standard pressure of 101.3kPa; – water reactive waste: waste which, in contact with water, emits flammable gases in dangerous quantities; – other flammable waste: flammable aerosols, flammable self-heating waste, flammable organic peroxides and flammable self-reactive waste. HP13 - "Sensitising:" waste which contains one or more substances known to cause sensitising effects to the skin or the respiratory organs.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number or ID number				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

14.6. Special precautions for user

Overland transport	: Not regulated
Transport by sea	: Not regulated
Air transport	: Not regulated
Inland waterway transport	: Not regulated
Rail transport	: Not regulated

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

REACH Annex XVII (Restriction List)

Contains no REACH substances with Annex XVII restrictions

REACH Annex XIV (Authorisation List)

Contains no REACH Annex XIV substances

REACH Candidate List (SVHC)

Contains no substance on the REACH candidate list

PIC Regulation (Prior Informed Consent)

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

POP Regulation (Persistent Organic Pollutants)

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Ozone Regulation (1005/2009)

Contains no substance subject to REGULATION (EU) No 1005/2009 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 September 2009 on substances that deplete the ozone layer.

Explosives Precursors Regulation (2019/1148)

Contains no substance subject to Regulation (EU) 2019/1148 of the European Parliament and of the Council of 20 June 2019 on the marketing and use of explosives precursors.

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on drug precursors)

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Full text of H- and EUH-statements:	
Acute Tox. 3 (Inhalation)	Acute toxicity (inhal.), Category 3
Acute Tox. 3 (Oral)	Acute toxicity (oral), Category 3
Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aquatic Chronic 2	Hazardous to the aquatic environment – Chronic Hazard, Category 2
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
H242	Heating may cause a fire.
H301	Toxic if swallowed.
H302	Harmful if swallowed.
H312	Harmful in contact with skin.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.

Safety Data Sheet

multicompPRO

H331	Toxic if inhaled.
H335	May cause respiratory irritation.
H373	May cause damage to organs through prolonged or repeated exposure.
H411	Toxic to aquatic life with long lasting effects.
Org. Perox. E	Organic Peroxides, Type E
Skin Corr. 1B	Skin corrosion/irritation, Category 1, Sub-Category 1B
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
Skin Sens. 1B	Skin sensitisation, category 1B
STOT RE 2	Specific target organ toxicity – Repeated exposure, Category 2
STOT SE 3	Specific target organ toxicity – Single exposure, Category 3, Respiratory tract irritation

Part Number

MP-IG74-50

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO