

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Relevant identified uses

No additional information available

### 1.2. Details of the supplier of the safety data sheet

Premier Farnell  
150 Armley Road  
Leeds LS12 2QQ  
Tel. : +44 (0) 8701 202530

#### Emergency telephone number

+44 1865 407333

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Serious eye damage/eye  
irritation, Category 2 : H319

Skin sensitisation, Category 1 : H317

Full text of H- and EUH-statements: see section 16

#### Adverse physicochemical, human health and environmental effects

Extremely flammable liquid and vapour. May cause respiratory irritation. May cause an allergic skin reaction. Causes serious eye irritation. May cause long lasting harmful effects to aquatic life.

### 2.2. Label elements

#### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)



GHS07

Signal word (CLP)

: Warning

Contains

: 2-Methyl-2-propenoic acid monoester with 1,2-propanediol; Acetic acid  
2-phenylhydrazide

Hazard statements (CLP)

: H317 - May cause an allergic skin reaction.  
H319 - Causes serious eye irritation.

Precautionary statements (CLP)

: P261 - Avoid breathing vapours.  
P280 - Wear protective gloves, eye protection, face protection.  
P321 - Specific treatment (see Take medical advice on this label).  
P333+P313 - If skin irritation or rash occurs: Get medical advice/attention.  
P337+P313 - If eye irritation persists: Get medical advice/attention.  
P362+P364 - Take off contaminated clothing and wash it before reuse.

### 2.3. Other hazards

PBT: not relevant – no registration required

vPvB: not relevant – no registration required

Contains no PBT/vPvB substances  $\geq 0.1\%$  assessed in accordance with REACH Annex XIII

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable

## 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
2-Methyl-2-propenoic acid monoester with 1,2-propanediol	CAS-No.: 27813-02-1 EC-No.: 248-666-3 REACH-no: 01-2119490226-37	≥10 – <20	Eye Irrit. 2, H319 Skin Sens. 1B, H317
Amorphous Silica substance with national workplace exposure limit(s) (AT, CZ, DE, EE, LV, SI, MK)	CAS-No.: 7631-86-9 EC-No.: 231-545-4 REACH-no: 01-2119379499-16	≥10 – <20	Not classified
α, α-dimethylbenzyl hydroperoxide substance with national workplace exposure limit(s) (LT, LV)	CAS-No.: 80-15-9 EC-No.: 201-254-7 EC Index-No.: 617-002-00-8 REACH-no: 01-2119475796-19	≥0.5 – <1	Org. Perox. E, H242 Acute Tox. 4 (Oral), H302 Acute Tox. 4 (Dermal), H312 Acute Tox. 3 (Inhalation), H331 Skin Corr. 1B, H314 Eye Dam. 1, H318 STOT RE 2, H373 Asp. Tox. 1, H304 Aquatic Chronic 2, H411
Acetic acid 2-phenylhydrazide	CAS-No.: 114-83-0	< 0.5 – <1	Acute Tox. 4 (Oral), H302 Skin Irrit. 2, H315 Eye Irrit. 2, H319 Skin Sens. 1, H317 STOT SE 3, H335

### Specific concentration limits:

Name	Product identifier	Specific concentration limits
α, α-dimethylbenzyl hydroperoxide	CAS-No.: 80-15-9 EC-No.: 201-254-7 EC Index-No.: 617-002-00-8 REACH-no: 01-2119475796-19	( 1 ≤C < 3) Eye Irrit. 2, H319 ( 1 <C < 10) STOT SE 3, H335 ( 3 ≤C < 10) Skin Irrit. 2, H315 ( 3 ≤C < 10) Eye Dam. 1, H318 ( 10 ≤C ≤ 100) Skin Corr. 1B, H314

Full text of H- and EUH-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

First-aid measures general	: Call a poison center or a doctor if you feel unwell.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing. Move the affected person away from the contaminated area and into the fresh air. If you feel unwell, seek medical advice. Call a poison center or a doctor if you feel unwell.
First-aid measures after skin contact	: Get medical advice/attention. Wash skin with plenty of water. Take off contaminated clothing. If skin irritation or rash occurs: Get medical advice/attention.
First-aid measures after eye contact	: Rinse immediately with plenty of water. Rinse cautiously with water for several minutes. If eye irritation persists: Get medical advice/attention. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion	: Rinse mouth out with water. Drink plenty of water. Do not induce vomiting. Call a poison center or a doctor if you feel unwell.

## 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after inhalation : May cause respiratory irritation.  
Symptoms/effects after skin contact : May cause an allergic skin reaction.  
Symptoms/effects after eye contact : redness, itching, tears.

## 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Suitable extinguishing media : Carbon dioxide. Foam. Water spray. Dry powder.

### 5.2. Special hazards arising from the substance or mixture

Fire hazard : Extremely flammable liquid and vapour.

Hazardous decomposition products in case of fire : Carbon dioxide. Carbon monoxide.

### 5.3. Advice for firefighters

Firefighting instructions : Use water spray or fog for cooling exposed containers.  
Protection during firefighting : Use self-contained breathing apparatus and chemically protective clothing. Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

General measures : Avoid contact with skin and eyes.

6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. Avoid contact with skin and eyes. Avoid breathing dust/fume/gas/mist/vapours/spray.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

### 6.2. Environmental precautions

Avoid release to the environment. Do not allow to enter drains or water courses.

### 6.3. Methods and material for containment and cleaning up

For containment : Collect spillage. Absorb spilled material with sand or earth.

Methods for cleaning up : Take up liquid spill into absorbent material. Clean up any spills as soon as possible, using an absorbent material to collect it. This material and its container must be disposed of in a safe way, and as per local legislation. Notify authorities if product enters sewers or public waters.

Other information : Dispose of materials or solid residues at an authorized site.

### 6.4. Reference to other sections

See Section 8. For further information refer to section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with eyes. Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking

and when leaving work. Do not eat, drink or smoke when using this product. Provide local exhaust or general room ventilation. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Ground/bond container and receiving equipment. Use only non-sparking tools. Take precautionary measures against static discharge. Flammable vapours may accumulate in the container. Use explosion-proof equipment. Wear personal protective equipment. Avoid breathing dust/fume/gas/mist/vapours/spray. Avoid contact with skin and eyes.

Hygiene measures : Take off immediately all contaminated clothing and wash it before reuse. Do not eat, drink or smoke when using this product. Wear personal protective equipment. Contaminated work clothing should not be allowed out of the workplace. Wash contaminated clothing before reuse. Always wash hands after handling the product.

## 7.2. Conditions for safe storage, including any incompatibilities

Technical measures : Ground/bond container and receiving equipment.

Storage conditions : Store in a closed container. Store locked up. Store in a well-ventilated place. Keep container tightly closed. Keep cool.

## 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

### 8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

#### Personal protective equipment:

Gloves. Safety glasses.

#### Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection : Safety glasses (EN 166). Protective goggles (EN 166). Safety glasses

8.2.2.2. Skin protection

Skin and body protection : Wear suitable protective clothing

Hand protection : Gloves

8.2.2.3. Respiratory protection

Respiratory protection : In case of insufficient ventilation, wear suitable respiratory equipment

## 8.2.2.4. Thermal hazards

No additional information available

## 8.2.3. Environmental exposure controls

Environmental exposure controls : Avoid release to the environment.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Yellow.
Odour	: Sweetish.
Odour threshold	: Not available
Melting point	: Not available
Freezing point	: Not available
Boiling point	: Not available
Flammability	: Not available
Explosive properties	: Not available
Oxidising properties	: Not available
Lower explosion limit	: Not available
Upper explosion limit	: Not available
Flash point	: >93°C
Auto-ignition temperature	: Not available
Decomposition temperature	: Not available
pH	: Not applicable
Viscosity, kinematic	: Not available
Viscosity, dynamic	: 80000 – 90000 cP
Solubility	: Miscible with : Organic solvents. Water: Slightly soluble in water.
Partition coefficient n-octanol/water (Log Kow)	: Not available
Vapour pressure	: Not available
Vapour pressure at 50°C	: Not available
Density	: Not available
Relative density	: 1.1 g/cm <sup>3</sup>
Relative vapour density at 20°C	: Not available
Particle characteristics	: Not applicable

### 9.2. Other information

#### 9.2.1. Information with regard to physical hazard classes

No additional information available

#### 9.2.2. Other safety characteristics

No additional information available

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Extremely flammable liquid and vapour.

## 10.2. Chemical stability

Stable under normal conditions of use. Stable under normal conditions.

## 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

## 10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7). Avoid contact with hot surfaces. Heat. No flames, no sparks. Eliminate all sources of ignition.

## 10.5. Incompatible materials

Strong acids.

## 10.6. Hazardous decomposition products

Carbon dioxide. Carbon monoxide. May liberate toxic gases.

## SECTION 11: Toxicological information

### 11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral) : Not classified

Acute toxicity (dermal) : Not classified

Acute toxicity (inhalation) : Not classified

2-Methyl-2-propenoic acid monoester with 1,2-propanediol (27813-02-1)	
LD50 oral rat	≥ 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 401 (Acute Oral Toxicity)
LD50 dermal rabbit	> 5000 mg/kg bodyweight Animal: rabbit, Animal sex: male
Amorphous Silica (7631-86-9)	
LD50 oral rat	3160 mg/kg Source: TOMES; HAZARDTEXT
LD50 dermal rabbit	> 5000 mg/kg Source: ECHA
LC50 Inhalation - Rat (Dust/Mist)	5.01 mg/l Source: ECHA
Skin corrosion/irritation	Not classified pH: Not applicable.
Amorphous Silica (7631-86-9)	
pH	3.5 – 4.4
Serious eye damage/irritation	Causes serious eye irritation. pH: Not applicable.
Amorphous Silica (7631-86-9)	
pH	3.5 – 4.4
Respiratory or skin sensitisation	May cause an allergic skin reaction.
Germ cell mutagenicity	Not classified
Carcinogenicity	Not classified
Amorphous Silica (7631-86-9)	
IARC group	3 - Not classifiable
Reproductive toxicity	Not classified
STOT-single exposure	Not classified
Acetic acid 2-phenylhydrazide (114-83-0)	
STOT-single exposure	May cause respiratory irritation.

STOT-repeated exposure	Not classified
<b>2-Methyl-2-propenoic acid monoester with 1,2-propanediol (27813-02-1)</b>	
LOAEC (inhalation, rat, gas, 90 days)	350 ppm Animal: rat, Guideline: OECD Guideline 413 (Subchronic Inhalation Toxicity: 90-Day Study), Remarks on results: other:
NOAEL (oral, rat, 90 days)	300 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)
NOAEC (inhalation, rat, gas, 90 days)	100 ppm Animal: rat, Guideline: OECD Guideline 413 (Subchronic Inhalation Toxicity: 90-Day Study), Remarks on results: other:
<b><math>\alpha</math>, <math>\alpha</math>-dimethylbenzyl hydroperoxide (80-15-9)</b>	
STOT-repeated exposure	May cause damage to organs through prolonged or repeated exposure.

Aspiration hazard : Not classified

## 11.2. Information on other hazards

No additional information available

## SECTION 12: Ecological information

### 12.1. Toxicity

Ecology - general : May cause long lasting harmful effects to aquatic life.

Hazardous to the aquatic environment, short-term (acute) : Not classified

Hazardous to the aquatic environment, long-term (chronic) : Not classified

Not rapidly degradable

Additional information : No data available.

<b>2-Methyl-2-propenoic acid monoester with 1,2-propanediol (27813-02-1)</b>	
LC50 - Fish [1]	233.174 mg/l Source: ECOSAR
EC50 - Crustacea [1]	> 143 mg/l Test organisms (species): Daphnia magna
EC50 72h - Algae [1]	> 97.2 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
NOEC (chronic)	45.2 mg/l Test organisms (species): Daphnia magna Duration: '21 d'
<b>Amorphous Silica (7631-86-9)</b>	
LC50 - Fish [1]	10000 mg/l Source: ECHA
EC50 - Crustacea [1]	> 5000 mg/l Source: ECHA
EC50 72h - Algae [1]	> 173.1 mg/l Source: ECHA

### 12.2. Persistence and degradability

Persistence and degradability : Biodegradability in water: no data available.

### 12.3. Bioaccumulative potential

Bioaccumulative potential : No bioaccumulation data available.

### 2-Methyl-2-propenoic acid monoester with 1,2-propanediol (27813-02-1)

Partition coefficient n-octanol/water (Log Pow) : 0.48

### Acetic acid 2-phenylhydrazide (114-83-0)

Partition coefficient n-octanol/water (Log Pow) : 0.7

## 12.4. Mobility in soil

No additional information available

## 12.5. Results of PBT and vPvB assessment

PBT: not relevant – no registration required

vPvB: not relevant – no registration required

## 12.6. Endocrine disrupting properties

No additional information available

## 12.7. Other adverse effects

Additional information : No other effects known

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

Product/Packaging disposal recommendations

: Avoid release to the environment.

Additional information

: Flammable vapours may accumulate in the container.

HP Code

: HP3 - "Flammable:"

– flammable liquid waste: liquid waste having a flash point below 60°C or waste gas oil, diesel and light heating oils having a flash point >55°C and ≤75°C;

– flammable pyrophoric liquid and solid waste: solid or liquid waste which, even in small quantities, is liable to ignite within five minutes after coming into contact with air;

– flammable solid waste: solid waste which is readily combustible or may cause or contribute to fire through friction; – flammable gaseous waste: gaseous waste which is flammable in air at 20 °C and a standard pressure of 101.3kPa;

– water reactive waste: waste which, in contact with water, emits flammable gases in dangerous quantities;

– other flammable waste: flammable aerosols, flammable self-heating waste, flammable organic peroxides and flammable self-reactive waste.

HP13 - "Sensitising:" waste which contains one or more substances known to cause sensitising effects to the skin or the respiratory organs.

## SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
<b>14.1. UN number or ID number</b>				
Not regulated for transport				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.2. UN proper shipping name</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.3. Transport hazard class(es)</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
<b>14.4. Packing group</b>				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated



14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

## 14.6. Special precautions for user

Overland transport	: Not regulated
Transport by sea	: Not regulated
Air transport	: Not regulated
Inland waterway transport	: Not regulated
Rail transport	: Not regulated

## 14.7. Maritime transport in bulk according to IMO instruments

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

REACH Annex XVII (Restriction List)

Contains no REACH substances with Annex XVII restrictions

REACH Annex XIV (Authorisation List)

Contains no REACH Annex XIV substances

REACH Candidate List (SVHC)

Contains no substance on the REACH candidate list

PIC Regulation (Prior Informed Consent)

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

POP Regulation (Persistent Organic Pollutants)

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Ozone Regulation (1005/2009)

Contains no substance subject to REGULATION (EU) No 1005/2009 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 September 2009 on substances that deplete the ozone layer.

Explosives Precursors Regulation (2019/1148)

Contains no substance subject to Regulation (EU) 2019/1148 of the European Parliament and of the Council of 20 June 2019 on the marketing and use of explosives precursors.

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on drug precursors)

#### 15.1.2. National regulations

No additional information available

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

Abbreviations and acronyms:	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways

# Safety Data Sheet

**multicomp**PRO

ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Full text of H- and EUH-statements:

Acute Tox. 3 (Inhalation)	Acute toxicity (inhal.), Category 3
Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Aquatic Chronic 2	Hazardous to the aquatic environment – Chronic Hazard, Category 2
Asp. Tox. 1	Aspiration hazard, Category 1

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp**PRO

# Safety Data Sheet

**multicomp**PRO

Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
H242	Heating may cause a fire.
H302	Harmful if swallowed.
H304	May be fatal if swallowed and enters airways.
H312	Harmful in contact with skin.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H331	Toxic if inhaled.
H335	May cause respiratory irritation.
H373	May cause damage to organs through prolonged or repeated exposure.
H411	Toxic to aquatic life with long lasting effects.
Org. Perox. E	Organic Peroxides, Type E
Skin Corr. 1B	Skin corrosion/irritation, Category 1, Sub-Category 1B
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
Skin Sens. 1B	Skin sensitisation, category 1B
STOT RE 2	Specific target organ toxicity – Repeated exposure, Category 2
STOT SE 3	Specific target organ toxicity – Single exposure, Category 3, Respiratory tract irritation

**Part Number**

MP-PS77-50

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp**PRO