

200A True RMS Fork Meter



General Characteristics

Power	: AAA 1.5V × 2
LCD Size	: 36.5mm × 24mm
Product Colour	Orange and Grey
Product Net Weight	: 163.7g
Product Size	: 210mm × 53mm × 35mm

Electrical Specifications

Basic Functions	Range	Best Accuracy
AC Current (A)	200A	±(2.5%+5)
DC Current (A)	200A	±(2.5%+5)
AC Voltage(V)	6V/60V/600V/750V	±(1.2%+3)
DC Voltage(V)	600mV/6V/60V/600V/1000V	±(0.8%+3)
Resistance (Ω)	600Ω/6kΩ/60kΩ/600kΩ/6MΩ/60MΩ	±(1.0%+2)
Capacitance (F)	60nF/600nF/6μF/60μF/600μF/6mF/60mF	±(4%+20)

Special Functions

Display Count	6000	√
Auto Range		√
True RMS		√
Diode	Around 3V	√
NCV		√
Data Hold		√
Zero & Relative Mode		√
LCD Backlight		√
Auto Power Off	Around 15 Minutes	√
Continuity Buzzer		√
Low Battery Indication	≤2.4V	√
Input Protection		
Input Impedance for DCV	≥10MΩ	

Accessories	Qty.	Note
Operating Manual	1 piece	-
Test Leads	1 pair	UL 18AWG Double insulated cable CAT III 1000V/CAT IV 600V 10A
Battery	2 pieces	1.5V AA × 2, replaceable
Cloth bag	1 piece	-

Part Number Table

Description	Part Number
200A True RMS Fork Meter	72-3545

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

