

Rechargeable LED Hand Lamp HL 701 A, IP 54, 700+100 lm

Bright, handy and compact.



Product number 1175640010
EAN 4007123691241

DESCRIPTION

- 12 super-bright SMD LEDs at the front.
- Additional switching stage for 1 SMD LED in the luminaire head.
- Stepless dimming function 10 % to 100 % for particularly long light duration.
- Rubberised handle for optimum grip.
- Foldable holding foot up to +/- 90° with integrated magnet.
- 2 magnets at the back and fold-out hook for flexible use.
- Li-Ion battery 3.7 V/2.0 Ah with charge indicator
- USB C charging interface, including USB C charging cable

TECHNICAL DATA

Luminous flux	700 lm	Number of batteries	1
Total luminous flux secondary source	100 lm	Battery type	Built-in battery pack
Colour temperature	5700 K	Battery technology	Lithium-ion
Colour rendering index	80-89 (class 1B)	Impact strength	IK07
Battery capacity	2 Ah	Protection class	III
Battery voltage	3.7 V	Degree of protection (IP)	IP54
Light duration max.	10 h	Colour	black
Battery charging time approx.	3.5 h		

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.36 kg
Weight of product (without packaging)	0.23 kg	Dimension LxWxH (incl. packing)	8.7 cm x 6.2 cm x 27.8 cm
Dimension LxWxH (without packing)	5.8 cm x 3.2 cm x 20.1 cm		

SCOPE OF DELIVERY

LED rechargeable hand lamp HL 701 A, 60cm USB C charging cable