


NOTICE OF PROPRIETARY RIGHTS THIS DOCUMENT CONTAINS CONFIDENTIAL TECHNICAL DATA, INCLUDING TRADE SECRETS, PROPRIETARY TO TIMES MICROWAVE SYSTEMS. DISCLOSURE OF THIS DATA IS EXPRESSLY CONDITIONED UPON YOUR ASSENT THAT ITS USE IS LIMITED TO USE WITHIN YOUR COMPANY ONLY. ANY OTHER USE IS STRICTLY PROHIBITED WITHOUT THE PRIOR WRITTEN CONSENT OF TIMES MICROWAVE SYSTEMS.

SYM	REVISION DESCRIPTION	DFTM	DATE	APPD	DATE
A	RELEASED FOR PRODUCTION	N. N. N	10/30/13	J. D. B.	11/1/13



CABLE PREPARATION
USE CST-240A (3192-152)
STRAIGHT SETTING.
CRIMP .255" HEX.

BODY	CONTACT
ALBALOY	GOLD/NI

1.0 PERFORMANCE
1.1 FREQUENCY RANGE: DC-6 GHz
1.2 NOMINAL IMPEDANCE: 50 OHMS
1.3 DWV: 750 VRMS @ 60 Hz (SEA LEVEL)
1.4 TEMPERATURE RANGE: -65°C TO +165°C

2.0 MATERIALS
2.1 DIELECTRIC: PTFE
2.2 CONTACTS: BERYLLIUM COPPER & BRASS
2.3 WASHER: PHOSPHOR BRONZE
2.4 CRIMP FERRULE: SOFT COPPER
2.5 OTHER METAL PARTS: BRASS
2.6 GASKET: SILICONE RUBBER
2.7 HEAT SHRINK: POLYOLEFIN THICK WALL

3.0 FINISHES: SEE TABLE
4.0 MECHANICAL
4.1 INTERFACE PER MIL-STD-348

MATL:		UNLESS OTHERWISE SPECIFIED		DFTM. N. N. N		TIMES MICROWAVE SYSTEMS			
		ALL DIMENSIONS ARE IN INCHES MACHINED SURFACES FINISH N/A RMS MAX. REMOVE ALL BURRS .005 MAX. BREAK MACHINE CORNERS .005 MAX. FILLET R. TOLERANCES ON DECIMALS .XX ± .03 .XXX ± .005 ANGLES ± 1° FRACTIONS ± 1/32		DATE 10/30/13					
CHKD. J. D. B.				TC-240-NF-BH-X N FEMALE BULKHEAD FOR LMR-240 CABLE					
DATE 11/1/13									
APPD. J. D. B.									
USED ON: A				DATE 11/1/13					
SCALE: N/A		DWG. SIZE A		DO NOT SCALE DRAWING		CODE IDENT 68999		DATE 11/1/13	
								SHEET 1 of 1 SD3190-2888	
						REV A			