

Encoder Controlled Single Channel Adjustable DC Power Supply



Characteristics		
Channels		Single Channel Adjustable
AC Input Voltage		230V $\pm 10\%$ / 50Hz, 110V, 220V $\pm 10\%$ / 60Hz
Output Voltage Range		0 - 30V
Output Current Range		0 - 5A
Load Regulation	Voltage	$\leq 0.01\% + 2\text{mV}$
	Current	$\leq 0.1\% + 5\text{mA}$
Line Regulation	Voltage	$\leq 0.01\% + 3\text{mV}$
	Current	$\leq 0.1\% + 3\text{mA}$
Setup Resolution	Voltage	10mV
	Current	1mA
Setup Accuracy (25°C $\pm 5^\circ\text{C}$)	Voltage	$\leq 0.5\% + 20\text{mV}$
	Current	$\leq 0.5\% + 10\text{mA}$
Ripple (20Hz - 20MHz)	Voltage	$\leq 2\text{m Vrms}$
	Current	$\leq 3\text{m Arms}$
Temperature Coefficient	Voltage	$\leq 150\text{ppm} + 10\text{mV}$
	Current	$\leq 150\text{ppm} + 5\text{mA}$
Read Back Accuracy	Voltage	10mV
	Current	1mA
Read Back Temperature Coefficient	Voltage	$\leq 150\text{ppm} + 10\text{mV}$
	Current	$\leq 150\text{ppm} + 5\text{mA}$
Reaction Time (10% Rated load)	Voltage Rise	$\leq 100\text{ms}$
	Current Drop	$\leq 100\text{ms}$
Accessories		User Manual
		Power Cord UK plug + EU plug, Diameter: 0.75mm ² $\times 3$, length: 1.2m
Weight		4.8kg
Dimension (W \times H \times D)		110mm \times 156mm \times 260mm

Part Number Table

Description	Part Number
Encoder Controlled Single Channel DC Power Supply, Adjustable, 150W	72-2690

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. TENMA is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands
Farnell.com/exclusive-brands
Element14.com/exclusive-brands

