




Part Number : 2271071114
Product Description : Pre-Crimped Lead CP-4.5-to-CP-4.5, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Black
Series Number : 227107
Status : Active
Product Category : Power and Signal Cable Assemblies



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies

Series	227107
Description	Pre-Crimped Lead CP-4.5-to-CP-4.5, Tin (Sn) Plating, 300.00mm Length, 16 AWG, Black
Application	Power, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	CP-4.5 Crimp Terminals
Keyword	Pre-Crimped Leads
Product Name	CP-4.5
UPC	198282672487

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Genderless-Genderless
Material - Metal	Copper Nickel
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	6.445/g
Packaging Type	Bag
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	PVC Insulated Bare Copper
Wire Insulation Diameter	2.90mm
Wire Size (AWG)	16

Use with Part(s)

Description	Part Number
-------------	-------------

CP-4.5 Dual Row Receptacle Housings	<u>206996</u>
CP-4.5 Dual Row Plug Housings	<u>206997</u>

This document was generated on Dec 18, 2024