

Mixer XGT®

UT001GZ02



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 500 / 920 min ⁻¹
Spindle Thread	M12 / M14
Blade diameter (beater)	240 mm
Sound Power Level (L _{WA})	92 dB(A)
Sound Pressure Level (L _{pA})	81 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Product net weight	5,1 kg
Tool weight with battery	5,7 - 7,0 kg
Product Dimensions (L x W x H):	373 x 458 x 235 mm

User benefits

- Soft start for smooth start-ups
- Ergonomic rubberised D-handle design for better fit and added comfort
- Battery cover minimizes the chance that spattered material might adhere to battery
- Battery protection system automatically shuts off power when the battery level is low

EAN 0088381774512

Link to product - www.makitauk.com



Related products

Standard AC

781006-4

Spanner 13 Mm



781010-3

Wrench 19



A-43717

Mixing Blade



A-43773

Mixing Blade Shaft 550 mm



Other

User manual

Parts drawing