

40VMax Multi Tool XGT®

TM001GZ02

10 000 - 20 000 min⁻¹

Model TM001G is a cordless multi tool powered by a 40VMax XGT Li-Ion battery and designed to be compatible with STARLOCK MAX accessories



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Orbits per Minute	10000 - 20000 min ⁻¹
Oscillation Angle	2 x 1,8 °
Pad size (triangle)	93 x 93 x 93 mm
Sound Pressure Level (L _{pA})	79 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Sanding	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Sanding	1,5 m/s ²
Vibration Level, Cutting With Plunge Cut Saw Blade	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Cutting With Plunge Cut Saw Blade	1,5 m/s ²
Vibration Level, Cutting With Segmental Saw Blade	≤ 2,5 m/s ²

EAN 0197050006837

Link to product - www.makitauk.com

User benefits

- Tool-less blade change for fast blade installation and removal
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- Built-in LED light with afterglow function illuminates the work area
- Soft start for smooth start-ups
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Anti-restart function minimises accidental start-up
- Brushless maintenance-free and long-life motor
- 12 Angle settings at every 30° from 0° to 360°



Related products

■ Standard AC

821551-8

Makpac case (3)



■ Other

User manual

Parts drawing