

Ratchet wrench LXT®

DWR180Z

18V • 3/8" / 1/4" • 47.5 Nm

Very agile and compact Ratchet Wrench LXT®

Ratchet wrench, for example, to assist in a garage 47.5 Nm torque with 3/8" or 1/4" mounting with two variable socket adapters. Bright LED - light to make work easier. Tool only, Battery and charger not included.



Technical specifications

Voltage LXT	✓
Nominal Battery Voltage	18 V
No load speed	0 - 800 min ⁻¹
Max. fastening torque Hard/Soft	47,5 Nm
Tightening Capacity Standard Bolt	M5 - M12
Tightening Capacity High Tensile Bolt	M5 - M10
Drive Square	3/8, 1/4 "
Sound Pressure Level (L _{pA})	77 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Product net weight	0,85 kg
Tool weight with battery	1,2 - 1,6 kg
Product Dimensions (L x W x H):	369 x 79 x 87 mm

User benefits

- Battery protection system automatically shuts off power when the battery level is low
- Built-in LED light with afterglow function illuminates the work area
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electric brake for maximum productivity and increased operator safety

EAN 0088381732871

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing