



Connectors > Contacts > Connector Contacts



Contact Type: **Pin**
Contact Mating Area Plating Material: **Tin**
Wire Contact Termination Area Plating Material: **Tin**
Contact Retention Within Housing: **With**
Contact Retention Type Within Housing: **Spring**

Features

Packaging Features

Packaging Quantity	4000
Packaging Method	Reel

Product Type Features

Discrete Wire Type	Solid or Stranded
Sealable	No

Dimensions

Compatible Insulation Diameter Range	2.03 – 2.54 mm[.08 – .1 in]
Wire Size	.8 – 1.4 mm²

Mechanical Attachment

Wire Insulation Support	With
Contact Retention Type Within Housing	Spring

Contact Features

Contact Underplating Material	Nickel
-------------------------------	--------



Contact Orientation	Straight
Mating Pin Diameter	1.57 mm[.062 in]
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	1.27 µm[50 µin]
Wire Contact Termination Area Plating Material Finish	Matte
Contact Shape & Form	Round
Contact Length	27.1 mm[1.067 in]
Wire Contact Termination Area Plating Thickness	1.27 µm[50 µin]
Barrel Type	Open
Contact Type	Pin
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Tin
Contact Retention Within Housing	With
Contact Size	Size 16
Contact Base Material	Brass
Contact Current Rating (Max)	13 A

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Usage Conditions

Operating Temperature Range	-55 – 90 °C[-67 – 194 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------




EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 796274-2
SLD CPC PLUG ASSY,17-16,STD SX




TE Part # 796188-1
SLD CPC PLUG ASSY,23-24,STD SX




TE Part # 796274-1
SLD CPC PLUG ASSY,17-16,STD SX



TE Part # 213853-1
CPC PLUG ASSEMBLY SIZE 23-19




TE Part # 208716-1
CMC PLUG ASSEMBLY,SZ 14



TE Part # 206516-1
CPC PLUG ASSEMBLY SIZE 11-4



TE Part # 1977878-1
SLD CPC PLUG ASY,11-4,STD SEX, UV RESIST



TE Part # 200893-2
INSERTION TOOL CONT



TE Part # 211770-2
CPC PLUG ASSEMBLY SIZE 23-19



TE Part # 213849-1
CPC PLUG ASSEMBLY SIZE 17-16



TE Part # 208718-2
CMC PLUG ASSEMBLY, SZ 14-5



TE Part # 5-2151023-1
OCEAN_2.0_Applicator-S-080F1200-RSM



TE Part # 796271-1
SLD CPC PLUG ASSY, 17-14, REV SX



TE Part # 208457-3
CMC PLUG ASSEMBLY, SZ 28-24



TE Part # 1977884-1
SLD CPC PLUG ASSY, 13-9, STD SEX, UV RESIS



TE Part # 539972-1
EXTRACTION TOOL



TE Part # 58495-2
PROCrimper DIE ASSY MULTIMATE



TE Part # 796450-1
PLUG ASSY, CPC, 17-9, REV SEX




TE Part # 796449-1
PLUG ASSY, CPC, 17-14, REV SEX




TE Part # 7-2266601-7
OC-080F1200-752-CRIMPTOOLINGKIT


Also in the Series | AMP Type III+



Connector Contacts(397)



Insertion & Extraction Tools(4)



Power Contacts(397)

Customers Also Bought



TE Part #1SNA216114R1200
FEET80





TE Part #2069578-1
MINI I/O PLUG CONN KIT(100 PC) D-2



TE Part #1SNA216110R2200
165LTTM5TM5



TE Part #880488-2
187 FASTON HSG. REC. 1P NATURAL



Documents

Product Drawings

III+ PIN,18-16,TIN STRIP

English

CAD Files

Customer View Model

ENG_CVM_1-66098-8_AE.3d_igs.zip

English

Customer View Model

ENG_CVM_1-66098-8_AE.3d_stp.zip

English

Customer View Model

ENG_CVM_1-66098-8_AE.2d_dxf.zip

English

3D PDF

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-66098-8_AP.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-66098-8_AP.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-66098-8_AP.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages
AMP Circular Connectors for Commercial Signal & Power Applications
English
M_SERIES_PIN_AND_SOCKET_CONNECTORS
English

Product Specifications
Application Specification
English