

Section 1: Chemical product and company identification

Product identifier

Product : Lithium Manganese Dioxide Battery

Details of the supplier of the safety data sheet

Premier Farnell
150 Armley Road
Leeds LS12 2QQ
Tel. : +44 (0) 8701 202530

Emergency telephone number

+44 1865 407333

Section 2: Hazards identification

This contains lithium, organic solvent, and other combustible materials. For this reason, improper handling of the battery could lead to distortion, leakage*, overheating, explosion of fire and cause human injury or equipment trouble. Please strictly observe safety instruction.

(*Leakage is defined as an unintended escape of liquid from a battery.)

Section 3: Composition/information of ingredients

Material	CAS No.	Content (%)
Manganese Dioxide	1313-13-9	16 - 37
Lithium metal	7439-93-2	1 - 3
1,2-Dimethoxyethane	110-71-4	2.6 - 5.8
Lithium perchlorate	7791-03-9	0.6 - 1.3
Propylene Carbonate	108-32-7	4.3 - 8
Graphite	7782-42-5 , 1333-86-4	1.8 - 5.5
Steel	7439-86-6 , 7440-47-3	30 - 85
Polypropylene	9003-07-0	0.5 - 10

Lithium content per cell model

Model	Weight of battery (in g)	Lithium content (in g)	Model	Weight of battery (in g)	Lithium content (in g)
CR1025	0.6	0.01	CR2320	3	0.038
CR1220	0.8	0.012	CR2330	4	0.076
CR1225	0.9	0.014	CR2335	4.3	0.08
CR1620	1.4	0.023	CR2430	4.6	0.086
CR1632	2	0.04	CR2450	6.9	0.168
CR2016	2	0.024	CR2477	10.5	0.286
CR2025	2.7	0.052	CR3032	6.8	0.136
CR2032	3.2	0.068	CR3832	8.8	0.18

Section 4: First aid measures

None unless internal materials exposure. If contents are leaked out, read the following instructions.

Inhalation	: Fumes can cause respiratory irritation. Remove to fresh air and consult a physician.
Skin	: Immediately flush skin plenty of water. If itch or irritation by chemical burn persists, consult a physician.
Eyes	: Immediately flush eye with plenty of water for at least 15 minutes. Consult a physician immediately
Ingestion	: If swallowing a battery, consult a physician immediately. If contents come into mouth, immediately rinse by plenty of water and consult a physician.

Section 5: Firefighting measures

Extinguishing agent	: Extinguisher of alkaline metal fire is effective. Plenty of cold water is also effective to cool the surrounding area and control the spread fire. But hydrogen gas may evolve by the reaction of water and lithium and it can form an explosive mixture. Therefore, in the case that lots of lithium batteries are burning in a confined space, use a smothering agent.
Firefighting procedure	: Use self-contained breathing apparatus and full protective gear not to inhale harmful gas.

Section 6: Accidental release measures

Accidental Releases	: Do not breathe vapors or touch liquid with bare hands (see section 4).
Waste Disposal Methods	: Evacuate area. If possible, a trained person should attempt to stop or contain the leak by neutralizing spill with soda lime or baking soda. A NIOSH Approved Acid Gas Filter Mask or Self-Contained Breathing Apparatus should be worn. Seal leaking battery and soda lime or baking soda in a plastic bag and dispose of as hazardous waste.
Other	: Follow North American Emergency Response Guide (NAERG)#138 for cells involved in an accident, cells that have vented, or have exploded.

Section 7: Handling and storage

1) Handling

- Never swallow.
- Never reverse the positive and negative terminals when mounting.
- Never short-circuit the battery.
- Never heat.
- Never expose to open flame.
- Never disassemble.
- Never weld the terminal or wire to the body of the battery directly.
- Never touch the liquid leaked out of battery.
- Never bring fire close to battery liquid.
- Never keep in touch with battery.

2) Storage

- Never let the battery contact with water.
- Never store the battery in hot and high humid place.

Section 8: Exposure controls and personal protection

Respiratory Protection	N/A	
Ventilation	Local Exhaust	N/A
	Mechanical	N/A
	Special	N/A
	Other	N/A
Eye Protection	N/A	
Protective Gloves	N/A	
Other protective clothing	N/A	

Section 9: Physical and chemical properties

Appearance	: Coin shape. Contents are sealed in stainless steel vessel
Nominal Voltage	: 3V
PH	: Not applicable because the article is not soluble in water
Boiling point/boiling range	: Not applicable for the article
Melting point	: Not applicable for the article
Decomposition Temperature	: Not applicable for the article
Flash point	: Not applicable for the article

Section 10: Stability and reactivity

Stability	: Stable
Incompatibility	: Water
Hazardous polymerization	: Will not occur
Condition to avoid	: See section 7
Hazardous decomposition or by products	: Hydrogen

Section 11: Toxicological information

Acute Toxicity:

1,2-Dimethoxyethane:

LC₅₀ (Inhalation): N/A

LD₅₀: N/A

Eye Effects: Corrosive

Skin Effects: Corrosive

Section 12: Ecological information

Aquatic Toxicity	: Do not let internal components enter marine environments. Avoid releases into waterways, wastewater, or groundwater.
------------------	--

Section 13: Disposal considerations

The battery disposal may be regulated by national or local government regulation. Please follow the instructions of proper regulation. As electric capacity is left in a discarded battery and it comes into contact with other metals, it could lead to distortion, leakage, overheating, or explosion, so make sure to cover the (+) and (-) terminals with friction tape or some other insulator before disposal.

Section 14: Transport information

In general, all cells/batteries being transported by ship, aircraft or railway, must be packaged in a safe and responsible manner. Do not leave them in high temperature or in high condensation. Battery cartons should be handled with care. Rough handling may result in batteries being short circuited or damaged.

Lithium metal cells and batteries are subject to the following transport rules. All Power Glory lithium cells/batteries meet the requirements of the special provisions listed below:

Regulatory Body	Special Provisions
ADR	188, 230, 310, 636, 656
IMDG	188, 230, 310, 957
UN	UN 3090, UN 3091
US DOT	29, A54, A100, A101
IATA, ICAO	Dangerous Goods Regulation (Packaging Instructions 968 – 970)

Ocean Transportation

All Power Glory lithium coin cells/batteries can be transported as Non-Dangerous Goods by vessel as these articles satisfy with SP188 of IMO-IMDG Code.

Air Transportation

Power Glory Lithium cells/batteries can meet the requirement of IATA Dangerous Goods Regulations 61st Edition of 2020 Packing Instruction PI 968 - 970.

Proper Shipping Name : Lithium Metal Batteries
UN Number : UN3090
(When cell/batteries contained in equipment / packed with equipment, it is UN3091)

Hazard Classification : Class 9 (Miscellaneous)

IATA DGR 61st Edition, Packing Instruction (PI)	Packing Instruction (PI) brief description
PI 968 Section IA	Cells, Cargo Aircraft only; net quantity per package Max. 35kg
PI 968 Section IB	Cells, Cargo Aircraft only; net quantity per package Max. 2.5kg
PI 968 Section II (until 31 March 2022)	Cells, Cargo Aircraft only, not more than one package in any single consignment; net quantity per package Max. 2.5kg
PI 969 Section I	Cells packed with equipment
PI 970 Section II	Cells contained in equipment, button cell batteries

- For cells, the lithium content cannot be more than 0.3g for PI 968 Section II (until 31 March 2022), not more than 1g for PI 968 Section IB, and can be more than 1g for PI 968 Section IA.
- Each cell is of the type proven to meet the requirements of each test in the UN Manual of Tests and Criteria, Part III, sub-section 38.3.
- Each cell is manufactured in good qualification factory.

Section 15: Regulatory information

Major applicable regulations for transportation are listed below:

- Technical Instructions for the Safety Transport of Dangerous Goods by Air, 2019-2020 Edition
- IATA Dangerous Goods Regulations 61st Edition (IATA DGR)
- IMO International Maritime Dangerous Goods Code 2018 Edition (IMO, IMDG Code)

Section 16: Other information

NA

Part Number
CR2016
CR2450
CR2430
CR2032FTH43-3
CR1220
CR2025
CR1632
CR2477
CR2032
CR2032FTV10-4
CR1620

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.