


SHARK 325W

Gel insulated join



Products may differ in size, colour and appearance to those shown. If you require further information or customisation, please contact us directly.



Material	Polyamide
Filling	Silicone
Temp. range min	-20 °C
Temp. range max	90 °C
Glow wire test	self-extinguishing
Voltage	0,6 kV - 1 kV
Quantity of cable	3
Type	SHARK 325W
UK-Number	SH0325W
WISKA-Order no.	10104876
Packing unit	1
ETIM-Classification	EC001169

Remarks:

Ampere: 6

Cable Size: 3 core

LxBxH: 47x86x27 mm

Description:

SHARK SMARTSHARK Pre-filled gel insulated straight joint. Includes 3 pole terminal block.

Additional Info:

Ready to use, re-enterable, no mixing or pouring, immediate operation, excellent electrical insulation, good mechanical strenght, no expiry date.

26.06.2025

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

☎ +44-12-08816062 · 📠 +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk