

THS155K6J ✓ ACTIVE

CGS | CGS THS

TE Internal #: 4-1879074-2

5.6K ohm Chassis Mount Resistor, 15 W, Wire Wound, 2

Terminations,  $\pm 30$  ppm/ $^{\circ}\text{C}$ , 5 %, Solder Lug, Loose Piece - Tray, 11 mm [.433 in] Height, CGS THS

[View on TE.com >](#)



Passive Components > Resistors > Chassis Mount Resistors > Power Resistor: Aluminum Housed, 75 Watt



Resistor Type: **Power Resistor**

Resistance Class: **1k $\Omega$  – 1M $\Omega$**

Resistance Value: **5.6K  $\Omega$**

Power Rating: **15 W**

Element Type: **Wire Wound**

[All Power Resistor: Aluminum Housed, 75 Watt \(236\)](#)

## Features

### Product Type Features

|               |                |
|---------------|----------------|
| Resistor Type | Power Resistor |
| Element Type  | Wire Wound     |

### Configuration Features

|                     |   |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

### Electrical Characteristics

|                             |                           |
|-----------------------------|---------------------------|
| Operating Voltage           | 265 VDC                   |
| Resistance Class            | 1k $\Omega$ – 1M $\Omega$ |
| Resistance Value            | 5.6K $\Omega$             |
| Power Rating                | 15 W                      |
| Passive Component Tolerance | 5 %                       |

### Termination Features

|                                         |            |
|-----------------------------------------|------------|
| Number of Terminations                  | 2          |
| Chassis Mount Resistor Termination Type | Solder Lug |

### Mechanical Attachment

|                          |                            |
|--------------------------|----------------------------|
| Panel Mount Feature Type | Flange with Mounting Holes |
|--------------------------|----------------------------|

### Dimensions



|                |                   |
|----------------|-------------------|
| Product Height | 11 mm[.433 in]    |
| Product Length | 36.5 mm[1.437 in] |
| Product Width  | 21 mm[.827 in]    |

### Usage Conditions

|                         |                            |
|-------------------------|----------------------------|
| Temperature Coefficient | $\pm 30$ ppm/ $^{\circ}$ C |
|-------------------------|----------------------------|

### Packaging Features

|                  |                    |
|------------------|--------------------|
| Packaging Method | Loose Piece - Tray |
|------------------|--------------------|

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

|                                               |                                                                                                                                |
|-----------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUNE 2024 (241)<br>Candidate List Declared Against: JUL 2021 (219)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Yet Reviewed for halogen content                                                                                           |
| Solder Process Capability                     | Hand solderable with lead free solder                                                                                          |

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



Also in the Series | **CGS THS**



Customers Also Bought



Documents

**Product Drawings**

**THS15 5K6 5%**

English

**CAD Files**

**3D PDF**

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1879074-2\\_BB.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1879074-2\\_BB.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_4-1879074-2\\_BB.3d\\_stp.zip](#)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[4-1773460-6\\_RESISTIVE\\_SOLUTIONS\\_RAIL](#)

English

[1309350\\_PASSIVE\\_COMPONENT](#)

English

[Aluminium Housed Power Resistors - Type THS Series - Tyco Electronics Passives](#)

English

[8-1773459-4\\_POWER\\_FILTERING\\_AND\\_RESISTIVE\\_SOLUTIONS\\_FOR\\_ELEVATORS\\_AND\\_ESCALATORS](#)

English