



Canvas Select Plus SD memory card

For Full HD 1080p video cameras

Kingston's Canvas Select Plus SD card delivers reliable performance with speeds of up to 150MB/s¹, ideal for cameras and Full HD video recording. With Class 10 UHS-I speeds, it ensures smooth and consistent performance. Durable and versatile, it's perfect for everyday storage needs.

- UHS-I speeds of up to 150MB/s¹
- Capture images and videos in Full HD (1080p)
- Capacities of up to 1TB²
- Durable³
- Lifetime warranty

Specifications

Capacities ²	64GB, 128GB, 256GB, 512GB, 1TB
Standard/Class	Class 10, UHS-I, U1/U3, Video Class 10/30
Performance ¹	64GB: 100MB/s read, UHS-I speed class, U1, V10 128GB-256GB: 150MB/s read, UHS-I speed class, U1, V10 512GB-1TB: 150MB/s read, UHS-I speed class, U3, V30
Dimensions	24mm x 32mm x 2.1mm
Format	exFAT
Operating temperature	-25°C~85°C
Storage temperature	-40°C~85°C
Voltage	3.3V
Warranty/support	Lifetime

Part Numbers SDS3

SDS3/64GB	SDS3/128GB	SDS3/256GB
SDS3/512GB	SDS3/1TB	

1. Based on internal testing; performance will vary based on host device. Engineered with proprietary technology to reach read speeds beyond UHS-I 104MB/s specification, up to 150MB/s. Write speed may be lower for some capacities. Full performance requires MobileLite Plus Reader.

2. Some of the listed capacity on a Flash storage device is used for formatting and other functions and thus is not available for data storage. As such, the actual available capacity for data storage is less than what is listed on the product. For more information go to Kingston's [Flash Memory Guide](#).

3. IEC/EN 60529 IPX7 certified for protection against continual water submersion for up to 30 minutes and a depth of up to 1m. Withstands temperature range from -25°C to 85°C. Protected against X-ray exposure based on ISO7816-1 guidelines.