

SAFETY DATA SHEET

SCRUBB Water Seal

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Trade name: SCRUBB Water Seal
Product no.: C11
Unique formula identifier (UFI): X200-U0CW-6002-Q0M6

1.2. Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture: Sealant
Uses advised against : None known.

1.3. Details of the supplier of the safety data sheet

Company and address: Orca Hygiene
Blackhouse Circle,
Blackhouse Industrial Estate,
AB42 1BN Peterhead
United Kingdom
Tel: +44 (0)1779 871945
E-mail: technical@orcahygiene.com
Revision: 13/05/2024
SDS Version: 1.0

1.4. Emergency telephone number

Contact The National Poisons Information Service (dial 111, 24 h service).
See section 4 "First aid measures".

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Eye Irrit. 2; H319, Causes serious eye irritation.

2.2. Label elements

Hazard pictogram(s):



Signal word: Warning

Hazard statement(s): Causes serious eye irritation. (H319)

Precautionary statement(s):

General:	Keep out of reach of children. (P102)
Prevention:	Wash hands thoroughly after handling. (P264)
Response:	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. (P305+P351+P338) If eye irritation persists: Get medical advice/attention. (P337+P313)
Storage:	-
Disposal:	-

Hazardous substances: None known.

Additional labelling: EUH208, Contains 1,2-benzisothiazol-3(2H)-one. May produce an allergic reaction.
UFI: X200-U0CW-6002-Q0M6

2.3. Other hazards

Additional warnings: This mixture/product does not contain any substances known to fulfil the criteria for PBT and vPvB classification.
This product does not contain any substances considered to be endocrine disruptors in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1. Substances

Not applicable. This product is a mixture.

3.2. Mixtures

Does not contain any substances required to report

See full text of H-phrases in section 16. Occupational exposure limits are listed in section 8, if these are available.

Other information

-

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

General information:	In the case of accident: Contact a doctor or casualty department – take the label or this safety data sheet. Contact a doctor if in doubt about the injured person's condition or if the symptoms persist. Never give an unconscious person water or other drink.
Inhalation:	Upon breathing difficulties or irritation of the respiratory tract: Bring the person into fresh air and stay with him/her.
Skin contact:	IF ON SKIN: Wash with plenty of water and soap.

	Remove contaminated clothing and shoes. Ensure to wash exposed skin thoroughly with water and soap. DO NOT use solvents or thinners. If skin irritation occurs: Get medical advice/attention.
Eye contact:	If in eyes: Flush eyes immediately with plenty of water or isotonic water (20-30 °C) for at least 5 minutes and continue until irritation stops. Remove contact lenses. Make sure to flush under upper and lower eyelids. If irritation continues, contact a doctor. Continue flushing during transport.
Ingestion:	If the person is conscious, rinse the mouth with water and stay with the person. Never give the person anything to drink. In case of malaise, seek medical advice immediately and bring the safety data sheet or label from the product. Do not induce vomiting, unless recommended by the doctor. Have the person lean forward with head down to avoid inhalation of or choking on vomited material.
Burns:	Not applicable.

4.2. Most important symptoms and effects, both acute and delayed

Sensitisation: This product contains substances, which may trigger allergic reaction upon dermal contact. Manifestation of allergic reactions typically takes place within 12-72 hours after exposure.

4.3. Indication of any immediate medical attention and special treatment needed

If eye irritation persists: Get medical advice/attention.

Information to medics

Bring this safety data sheet or the label from this product.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Suitable extinguishing media: Alcohol-resistant foam, carbon dioxide, powder, water mist. Unsuitable extinguishing media: Waterjets should not be used, since they can spread the fire.

5.2. Special hazards arising from the substance or mixture

Fire will result in dense smoke. Exposure to combustion products may harm your health. Closed containers, which are exposed to fire, should be cooled with water. Do not allow fire-extinguishing water to enter the sewage system and nearby surface waters.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and protective clothing to prevent contact. Upon direct exposure contact The National Poisons Information Service (dial 111, 24 h service) in order to obtain further advice.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Contaminated areas may be slippery.

6.2. Environmental precautions

Avoid discharge to lakes, streams, sewers, etc.
Keep unauthorized persons away from the spill

6.3. Methods and material for containment and cleaning up

Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations.



According to REACH Regulation (EC) No 1907/2006, as retained and amended SI 2019/758 and SI 2020/1577

Wherever possible cleaning should be performed with normal cleaning agents. Avoid use of solvents.

6.4. Reference to other sections

See section 13 "Disposal considerations" on handling of waste.

See section 8 "Exposure controls/personal protection" for protective measures.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Smoking, drinking and consumption of food is not allowed in the work area.

See section 8 "Exposure controls/personal protection" for information on personal protection.

7.2. Conditions for safe storage, including any incompatibilities

Containers that have been opened must be carefully resealed and kept upright to prevent leakage.

Recommended storage material: Always store in containers of the same material as the original container.

Storage temperature: No specific requirements

Incompatible materials: Strong acids, strong bases, strong oxidizing agents, and strong reducing agents.

7.3. Specific end use(s)

This product should only be used for applications quoted in section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

No substances are listed in the national list of substances with an occupational exposure limit.

DNEL

No data available.

PNEC

No data available.

8.2. Exposure controls

Apply general control to prevent unnecessary exposure

General recommendations: Smoking, drinking and consumption of food is not allowed in the work area.

Exposure scenarios: There are no exposure scenarios implemented for this product.

Exposure limits: Occupational exposure limits have not been defined for the substances in this product.

Appropriate technical measures: Apply standard precautions during use of the product. Avoid inhalation of vapours.

Hygiene measures: In between use of the product and at the end of the working day all exposed areas of the body must be washed thoroughly. Pay special attention to hands, forearms and face.

Measures to avoid environmental exposure: No specific requirements.

Individual protection measures, such as personal protective equipment

Generally: No specific requirements

Respiratory Equipment:

No specific requirements

Skin protection:

No specific requirements.

Hand protection:

No specific requirements.

Eye protection:

No specific requirements.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	White
Odour / Odour threshold:	Characteristic
pH:	6 - 8
Density (g/cm³):	-
Relative density:	1 (20 °C)
Kinematic viscosity:	Testing not relevant or not possible due to the nature of the product.
Particle characteristics:	Does not apply to liquids.

Phase changes

Melting point/Freezing point (°C):	Testing not relevant or not possible due to the nature of the product.
Softening point/range (waxes and pastes) (°C):	Does not apply to liquids.
Boiling point (°C):	Testing not relevant or not possible due to the nature of the product.
Vapour pressure:	Testing not relevant or not possible due to the nature of the product.
Relative vapour density:	Testing not relevant or not possible due to the nature of the product.
Decomposition temperature (°C):	Testing not relevant or not possible due to the nature of the product.

Data on fire and explosion hazards

Flash point (°C):	Testing not relevant or not possible due to the nature of the product.
Flammability (°C):	Testing not relevant or not possible due to the nature of the product.
Auto-ignition temperature (°C):	Testing not relevant or not possible due to the nature of the product.
Lower and upper explosion limit (% v/v):	Testing not relevant or not possible due to the nature of the product.

Solubility

Solubility in water:	Testing not relevant or not possible due to the nature of the product.
n-octanol/water coefficient (LogKow):	Testing not relevant or not possible due to the nature of the product.
Solubility in fat (g/L):	Testing not relevant or not possible due to the nature of the product.

9.2. Other information

Oxidizing properties: Testing not relevant or not possible due to the nature of the product.
Other physical and chemical parameters: No data available.

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

No data available.

10.2. Chemical stability

The product is stable under the conditions, noted in section 7 "Handling and storage".

10.3. Possibility of hazardous reactions

None known.

10.4. Conditions to avoid

None known.

10.5. Incompatible materials

Strong acids, strong bases, strong oxidizing agents, and strong reducing agents.

10.6. Hazardous decomposition products

The product is not degraded when used as specified in section 1.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008 as retained and amended in UK law

Acute toxicity

Based on available data, the classification criteria are not met.

Skin corrosion/irritation

Based on available data, the classification criteria are not met.

Serious eye damage/irritation

Causes serious eye irritation.

Respiratory sensitisation

Based on available data, the classification criteria are not met.

Skin sensitisation

Based on available data, the classification criteria are not met.

Germ cell mutagenicity

Based on available data, the classification criteria are not met.

Carcinogenicity

Based on available data, the classification criteria are not met.

Reproductive toxicity

Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

11.2. Information on other hazards

Long term effects

Irritation effects: This product contains substances, which may cause irritation upon exposure to skin, eyes or lungs. Exposure may result in an increased absorption potential of other hazardous substances at the area of exposure.

Endocrine disrupting properties

This mixture/product does not contain any substances known to have hormone-disrupting properties in relation to health.

Other information

None known.

SECTION 12: ECOLOGICAL INFORMATION

12.1. Toxicity

No data available.

12.2. Persistence and degradability

Based on available data, the classification criteria are not met.

12.3. Bioaccumulative potential

Based on available data, the classification criteria are not met.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

This mixture/product does not contain any substances known to fulfil the criteria for PBT and vPvB classification.

12.6. Endocrine disrupting properties

This mixture/product does not contain any substances considered to have endocrine-disrupting properties in relation to the environment.

12.7. Other adverse effects

None known.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste treatment methods

Product is not covered by regulations on dangerous waste.
Dispose of contents/container to an approved waste disposal plant.
Regulation (EU) No 1357/2014 of 18 December 2014 on waste as retained and amended in UK law.

EWC code

Not applicable.

Specific labelling

Contaminated packing

Packaging containing residues of the product must be disposed of similarly to the product.

SECTION 14: TRANSPORT INFORMATION

	14.1 UN / ID	14.2 UN proper shipping name	14.3 Hazard class(es)	14.4 PG*	14.5 Env**	Other information:
ADR	-	-	-	-	-	-
IMDG	-	-	-	-	-	-
IATA	-	-	-	-	-	-

* Packing group

** Environmental hazards

Additional information

Not dangerous goods according to ADR, IATA and IMDG.

14.6. Special precautions for user

Not applicable.

14.7. Maritime transport in bulk according to IMO instruments

No data available.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Restrictions for application: No special.

Demands for specific education: No specific requirements.

SEVESO - Categories / dangerous substances: Not applicable.

Additional information: Not applicable.

Sources: Regulation (EU) No 1357/2014 of 18 December 2014 on waste as retained and amended in UK law.
Regulation (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures (CLP) as retained and amended in UK law.
Regulation (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) as retained and amended in UK law.

15.2. Chemical safety assessment

No

SECTION 16: OTHER INFORMATION

Abbreviations and acronyms

ADN = European Provisions concerning the International Carriage of Dangerous Goods by Inland Waterway

ADR = The European Agreement concerning the International Carriage of Dangerous Goods by Road

ATE = Acute Toxicity Estimate

BCF = Bioconcentration Factor
CAS = Chemical Abstracts Service
CE = Conformité Européenne (European conformity)
CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
CSA = Chemical Safety Assessment
CSR = Chemical Safety Report
DMEL = Derived Minimal Effect Level
DNEL = Derived No Effect Level
EINECS = European Inventory of Existing Commercial chemical Substances
ES = Exposure Scenario
EUH statement = CLP-specific Hazard statement
EuPCS = European Product Categorisation System
EWC = European Waste Catalogue
GHS = Globally Harmonized System of Classification and Labelling of Chemicals
GWP = Global warming potential
IARC = International Agency for Research on Cancer (IARC)
IATA = International Air Transport Association
IBC = Intermediate Bulk Container
IMDG = International Maritime Dangerous Goods
LogPow = logarithm of the octanol/water partition coefficient
MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
OECD = Organisation for Economic Co-operation and Development
PBT = Persistent, Bioaccumulative and Toxic
PNEC = Predicted No Effect Concentration
RID = The Regulations concerning the International Carriage of Dangerous Goods by Rail
RRN = REACH Registration Number
SCL = A specific concentration limit
SVHC = Substances of Very High Concern
STOT-RE = Specific Target Organ Toxicity - Repeated Exposure
STOT-SE = Specific Target Organ Toxicity - Single Exposure
TWA = Time weighted average
UN = United Nations
UVBC = Unknown or variable composition, complex reaction products or of biological materials
VOC = Volatile Organic Compound
vPvB = Very Persistent and Very Bioaccumulative

Additional information

The classification of the substance/mixture in regard of health hazards are in accordance with the calculation methods given by Regulation (EC) No. 1272/2008 (CLP) as retained and amended in UK law.

The safety data sheet is validated by

OHL

Other

A change (in proportion to the last essential change (first cipher in SDS version, see section 1)) is marked with a triangle.

The information in this safety data sheet applies only to this specific product (mentioned in section 1) and is not necessarily correct for use with other chemicals/products.

It is recommended to hand over this safety data sheet to the actual user of the product. Information in this safety data sheet cannot be used as a product specification.

Country-language: GB-en