

# AIRCOM 126

## 2.4 GHz 126 Channel Wireless DMX Unit

Aircom 126 transmits and receives standard DMX 512 protocol data by wireless way, which solve lighting control issues of wireless communication between lighting controllers and fixtures. It gets rid of relying on connecting cables completely, and also can ensure without any time delay when signal data is real time and reliable.

It adopts global free 2.4GHz ISM frequency band and high effective GFSK modulation. Communication design is in 126 channels jumping frequency with high anti-jamming ability. The product is therefore applied in many contexts, such as stage lighting disco hall, gymnasium lighting, portable stage performance, conference centers, theme parks, bar lighting, and so on. In short, a really useful tool to solve DMX connection problems quickly.



## PRODUCT DETAILS

### Key features

Both Transmitting and Receiving operation within same unit

One transmitter can manage more receivers at the same time

7 groups ID code set table, User can use 7 groups individual wireless nets without any interfere each other in the same place

Each net contains 512 DMX channels

126 channels jumping frequency (7 groups x 16 channel frequencies) to avoid interferences

High anti-jamming ability to ensure working reliability

<b>Work frequency range</b>	2.4 GHz ISM band (no license needed)
-----------------------------	--------------------------------------

<b>Communication distance</b>	300 m
-------------------------------	-------

Tricolor LED displaying for easy setup

High quality power supply stage for maximum stability at wider range voltage input

## Specifications

<b>Frequency Band</b>	2.4 GHz ISM
<b>Modulation Type</b>	GFSK Modulation
<b>Frequency range</b>	24,000 ~ 24,835 GHz
<b>Channel Frequencies</b>	126 jumping frequencies
<b>Communication Distance</b>	300 m
<b>Receiver Sensibility</b>	-106 dBm
<b>Transmission Power</b>	20 dBm
<b>Antenna</b>	100 mm helical SMA antenna
<b>Protocols</b>	DMX512
<b>Number of DMX Channels</b>	512 Channels within each ID
<b>Power Input</b>	AC88 ~ 256 Vac - 50/60 Hz
<b>Data Input/Outputs</b>	3-pin XLR male (In) female (out) sockets
<b>Data Pin Configuration</b>	Pin 1 shield, Pin 2 (-), Pin 3 (+)
<b>Unit Size (WxHxD)</b>	150x50x76 mm - 5.90 x 1.97 x 2.99 in
<b>Unit Net Weight 0.27 kg - 0.59 lbs.</b>	
<b>Packing Size (WxHxD)</b>	175x87x98 mm - 6.89 x 3.42 x 3.86 in
<b>Packing Gross Weight</b>	0.5 kg - 1.10 lbs.