

Desk Mount Dual Monitor Arm with Crossbar, Up To 27" Displays, VESA 75x75/100x100, Max 33lb/15kg, C-Clamp, Fully Articulating, Mechanical Spring, TAA

**Product ID:** H2M1AS2-MONITOR-ARM



This crossbar monitor desk mount is designed to support up to two 27-inch displays, creating an ergonomic multi-monitor setup that provides an extensive viewing area for productivity. The built-in handle enables moving all monitors simultaneously, while the spring-assisted arm enables multiple adjustments to suit different ergonomic needs.

The mechanical spring arm enables toolless height adjustment of up to 12.9in (32.7cm) with effortless one-touch motion. The maximum arm extension is 22.6in (57.4cm) and a total weigh capacity of 33lb (15kg).

This monitor mount is ideal for bezel-less or slim bezel displays, creating a more extensive and seamless viewing experience that enhances multitasking and productivity. The VESA mounts can slide along the crossbar, allowing for further adjustments.

The monitors' VESA mounts enable support +/-15 swivel, +65/-15 tilt, and 360 screen rotation for portrait/landscape orientation.

To maintain an organized workspace, the arms feature a cable management channel along the underside to keep cables out of sight, reducing clutter and contributing to a tidy setup.

## Certifications, Reports and Compatibility



## Applications

## Features

- **DESK MOUNT MONITOR ARM:** Dual monitor mount for up to 27-inch displays; Max 33lb (15kg); VESA plate supports 75x75/100x100mm Patterns; Crossbar keeps monitors perfectly aligned at all times; Articulating mechanical spring arm; TAA-compliant
- **SYNCHRONIZED MOVEMENT:** Crossbar design with built-in handle enables moving the dual monitor setup without realigning the monitors; Monitor stand includes tools to adjust arm tension; Max arm extension 22.6in (57.4cm), height range 7.9-20.8in (20.2-52.9cm)
- **MECHANICAL SPRING ONE-TOUCH ADJUSTMENT:** Full-motion arm features a high-quality mechanical spring for smooth and effortless one-touch motion; Mechanical springs are more robust and resistant to wear over time compared to gas springs; Backed for 10 years
- **DISPLAY ADJUSTMENT:** Ergonomic dual-monitor mount w/toolless adjustments of +/-15 swivel, +65/-15 tilt, & 360 screen rotation (portrait/landscape); The crossbar swivels +/-90, spring arm supports 360 rotation, & swivel arm supports 180 rotation
- **ORGANIZED WORKSPACE:** Cable management channels along the arms of the multi-monitor mount keep cables organized and out of sight, while a cable clip at the base helps maintains a tidy setup; Thumb screws included for tool-less monitor mounting

---

### Hardware

Warranty	10 Years
Wallmountable	No
Cable Management	Yes
Tools Included	Yes
Articulating	Yes
# of Displays Supported	2
Mounting Options	Desk & Grommet Clamp
VESA Hole Pattern(s)	75x75 mm 100x100 mm
Mounting Surface Thickness	Desk Clamp: Table Thickness 0.8 - 2.3in (2 - 6cm)

---

### Performance

Weight Capacity (Per Display)	33.1 lb [15 kg]
Minimum Display Size	17"

Maximum Display Size	27"
Fits Curved Display	No
Fits UltraWide Displays	No
Height Adjustment	Yes
Minimum Height	8.0 in [202 mm]
Maximum Height	20.8 in [529 mm]
Minimum Arm Extension	6.3 in [160 mm]
Maximum Arm Extension	22.6 in [574 mm]
Display Tilt	+65 / -15
Display Swivel	+/-15
Swivel / Pivot	+180 / -180
Display Rotation	360
Anti-theft	No

---

#### Physical Characteristics

Color	Black
Construction Material	Aluminum, Steel, and Plastic
Product Length	31.5 in [80 cm]
Product Width	13.8 in [35 cm]
Product Height	20.8 in [52.9 cm]
Weight of Product	13.2 lb [6.0 kg]

---

#### Packaging Information

Package Length	13.9 in [35.2 cm]
Package Width	31.5 in [80.0 cm]
Package Height	6.7 in [17.1 cm]
Shipping (Package) Weight	13.8 lb [6.3 kg]

---

## What's in the Box

Included in Package	1 - Monitor Arm
	1 - Base EVA Cushion
	2 - VESA Monitor Mount
	8 - VESA Screws
	1 - Cable Clip
	1 - M3 Hex Key
	1 - M6 Hex Key
	1 - Crossbar
	2 - Crossbar Endcaps
	4 - M6x12 Screws
	4 - M6 Cap Nuts
	1 - Grab Handle
	1 - Quick-Start Guide

---

## Warranty Information

Warranty	10 Years
----------	----------

---

***\*Product appearance and specifications are subject to change without notice.***