



DCE050N-XJ – 18V XR TRANSFER PUMP – Body Only

Ideal for the mechanical and plumbing trades, the 18V XR Transfer Pump (battery and charger sold separately) can transfer large amounts of water or water/glycol mixture to be used for a wide range of applications. Engineered with a self priming pump and a LED-embedded power switch, this cordless solution delivers quick performance and is designed with the ability to transfer a 60% water/40% propylene glycol mixture. Featuring an exceptional flow rate, lift, and head height, this tool offers a convenient lightweight construction for anyone needing to move water.



Features and Benefits:

- **AUTO-SHUTOFF** – To prevent the unit running dry and being damaged.
- **REMOVEABLE IMPELLER WINDOW** – Allowing you to check/clear debris and replace the impeller if required.
- **OPERATIONAL IN BOTH HORIZONTAL AND VERTICAL ORIENTATION.**
- **RUBBER BASE** – To reduce vibration and sliding.
- **IPX4 RATED** – Water resistant design with a self-closing battery well.

Specifications:

- Power Source – Cordless
- Battery Technology – Lithium ion
- Voltage – 18V
- Weight -
- $\frac{3}{4}$ " BSPT Male thread connectors
- Max. flowrate – 38 L/min
- Max. lift height – 7.5 m
- Max. head height – 17 L/min at 13.7 m
- Litres per charge* - 1137 L
- Water temperature range - 0° C – 60 ° C
- Max. operating air temperature – 40 ° C

Supplied with:

- DCE050 Transfer pump body
- 2 x Stainless steel adaptors