





4	BLACK PVC TUBE $\phi 3.0 \times 30$ mm	2	M743
	ALUMINUM FOIL 33*110mm	2	M379
	MOLDED PE COLOR TRANSPARENT		TWN
	MOLDED PVC BEIGE		M304
3	NON-UL 25C 28AWG, ALUM-MYLAR FOIL SHIELDING WITH DRAIN WIRE, OD 7.0mm, JACKET BEIGE	L-10mm	M304
2	MOLDED THUMBSCREW #4-40, LENGTH 46.5mm, BEIGE	4	M95
1	DB25 MALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	2	M108
No.	DESCRIPTION	Q'TY	Supplier
APPROVED	SL-102 SL-103 SL-105 SL-107 SL-110		Cable Length Unless Other Spec. Tolerances: 0 ~200mm ±10mm 201~1000mm ±20mm 1001 ~1500mm ±25mm 1501~2100mm ±30mm 2100mm↑ ±40mm
CHECKED			
DRAWING			
DATE			
03/MAR/06		ITEM NO.	
UNIT:mm			

CHECKED