






Data Sheet | Item Number: 221-529/000-006

Mounting carrier with strain relief; for 10-wire connectors; 221 Series - 4 mm²; with snap-in mounting foot; blue

<https://www.wago.com/221-529/000-006>



Color: ■ blue





Physical data		
Width		38.3 mm / 1.508 inches
Height		59.5 mm / 2.343 inches
Height from the surface		55 mm / 2.165 inches
Depth		23.7 mm / 0.933 inches

Mechanical data		
Mounting type		Snap-in foot with snap-in mounting foot for vertical mounting
Suitable		for 10-wire connectors (4 mm²)

Material data		
Note (material data)		Information on material specifications can be found here
Color		blue
Material group		I
Insulation material (main housing)		Polyamide (PA66)
Flammability class per UL94		V0
Fire load		0.183 MJ
Weight		6.1 g

Commercial data		
PU (SPU)		10 pcs
Packaging type		Box
Country of origin		CN
GTIN		4066966603811
Customs tariff number		39269097900

Product classification		
UNSPSC		39121410
ETIM 9.0		EC002848
ECCN		NO US CLASSIFICATION

Environmental Product Compliance		
RoHS Compliance Status		Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance
221-529/000-006

↓



1 Compatible Products
1.1 Optional Accessories
1.1.1 Marking
1.1.1.1 Marking strip



Item No.: 210-833
Marking strips; 25 m on roll; 6 mm wide;
plain; Self-adhesive; white