


Color: ■ blue



Electrical data

Ratings per IEC/EN

Nominal voltage (III/3)	400 V
Rated current	41 A

Physical data

Width	12.3 mm / 0.484 inches
Height	10.74 mm / 0.423 inches
Depth	23.9 mm / 0.941 inches
Jumper assignment	1-2

Mechanical data

Use	with locking
-----	--------------

Material data

Note (material data)	Information on material specifications can be found here
Color	blue
Insulation material (main housing)	Polyamide (PA66)
Fire load	0 MJ
Weight of insulation material	0.45 g
Weight	2.9 g

Environmental requirements

Continuous operating temperature	-60 ... +105 °C
----------------------------------	-----------------

Commercial data

PU (SPU)	5 pcs
Packaging type	Bag
Country of origin	CN
GTIN	4055144068016
Customs tariff number	85366990990

Product classification

UNSPSC	39121421
ETIM 9.0	EC000489
ETIM 8.0	EC000489
ECCN	NO US CLASSIFICATION

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Downloads

Environmental Product Compliance

[Compliance Search](#)

Environmental Product
Compliance
221-941/000-006



Documentation

Bid Text

221-941/000-006

xml
2.96 KB

221-941/000-006

docx
27.51 KB


CAD/CAE-Data

CAD data

2D/3D Models
221-941/000-006


Installation Notes

Commoning



Extending the N and PE (ground) distribution via jumper

Commoning




Insert the jumper with a locking function into closed clamping units.

Commoning



With a locking function:
The lockable jumper is plugged into the splicing connectors.

Commoning



The lockable jumper is plugged into the splicing connectors.

Commoning



Remove the locking mechanism for intentional jumper removal.



Remove the jumper from open clamping units.