

2 Piece Combo Kit XGT®

DK0176G205

40V

Includes TD003G Brushless Impact Driver, HP001G
Brushless Combi Drill



Models in kit



Combi Drill XGT®
HP001G



Impact Driver XGT®, 40Vmax
TD003G

Combi Drill XGT®

HP001G

40V max • 140 Nm • 0 – 2 600 min⁻¹

Rugged, brushless combi drill for heavy-duty screwdriving and drilling

A powerful, brushless drill for professional screwdriving and drilling with or without hammer action, two power settings. A high maximum torque of 140 / 68 Nm. An ideal choice for jobs that require high power and torque. Integrated LED light.



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	0 - 650 / 2600 min ⁻¹
Max. fastening torque Hard/Soft	140 / 68 Nm
Torque setting	41 / 21
Impacts per Minute (IPM)	0 - 9750 / 39000 min ⁻¹
Max. Drilling Diameter in Masonry	20 mm
Max. Drilling Diameter in Steel	20 mm
Driving Shank	1/2"-20UNF "
Drill Chuck Capacity	1,5 - 13 mm
Sound Power Level (L _{WA})	96 dB(A)
Sound Pressure Level (L _{pA})	85 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	2,7 - 3,9 kg

User benefits

- Jog selector for easy adjustment of mounting torque, visual confirmation of the selected torque on the digital display
- Battery protection system automatically shuts off power when the battery level is low
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops

Link to product - www.makita.com





Impact Driver XGT®, 40Vmax TD003G

1/4", 210 Nm, 0 – 3 700 min⁻¹

Model TD003G is a cordless impact driver powered by 40Vmax XGT® Li-Ion battery

It features a combination of sufficient fastening performance and high cost-competitiveness achieved by carefully selecting the functions. The main features and benefits are: •Aluminum hammer case + Black bumper •Impact power selection: · 4 modes (Max/ Hard/ Med./ Soft for bolt) · 1 T-mode (for thin metal only)



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	0 - 1100 / 2100 / 3200 / 3700 min ⁻¹
Max Fastening Torque Impact Drill	20 / 50 / 170 / 210 Nm
Tightening Capacity Standard Bolt	M5 - M16
Impacts per Minute (IPM)	0 - 1400 / 2600 / 3600 / 4100 min ⁻¹
Sound Power Level (L _{WA})	106 dB(A)
Sound Pressure Level (L _{pA})	95 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,7 - 2,9 kg
Product Dimensions (L x W x H):	121 x 86 x 252 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-	Li-ion

User benefits

- LED light illuminates the work site
- Low power consumption thanks to brushless motor
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- The rubber grip on the handle ensures a good working grip
- Battery protection system automatically shuts off power when the battery level is low
- Anti wobbling bit structure

Link to product - www.makitauk.com



Related products kit

Standard AC

821551-8
Makpac case (3)



Standard MA

BL4025 (2x)
Battery XGT® 2,5 Ah



DC40RA
Battery Charger XGT®



Optional AC

122576-8
Stopper Pole



127551-9
Grip Assembly



346317-0
Belt Hook



452947-8
Bitholder



763252-1
Keyless Drill Chuck



784637-8
Screw Bit, Ph2 – S6, 45 Mm, Double



821551-8
Makpac case (3)



835F93-2
Inner tray (3)



Other - HP001G

User manual

Parts drawing

Other - TD003G

User manual

Parts drawing

Battery Charger XGT®

DC40RA

Li-ion • 40Vmax • DC40RA

Charger for XGT® 40Vmax batteries.

Rapid charger for XGT® 40Vmax slide-style batteries. Cooling fans cool the battery and charger circuit board during charging, allowing faster charging. Charging optimised in terms of voltage, current and temperature. Charges a battery in 28-45 minutes, depending on the battery's capacity.



Technical specifications

Nominal Battery Voltage	40 V
Average Charging Time	22 - 50 min
Charging Time 2.0 Ah	22 min
Charging Time 2.5 Ah	28 min
Charging Time 4.0 Ah	45 min
Charging Time 5.0 Ah	50 min
Charging Time 8.0 Ah	76 min
Continuous Input Power	310 W
Power Supply Cord	2,0 m
Product Dimensions (L x W x H):	156 x 210 x 84 mm
Voltage XGT	✓
Product net weight	1,0 kg

User benefits

- Equipped with two cooling fans, one for battery and the other for charging circuit
- Compatible with Interchangeable adapter ADP10 for charging LXT Li-Ion batteries
- New charging status indicator light, enlarged and raised for clearer indication
- Selectable melody sound for full charge notification
- Also works as a wall-mounted charger
- Able to perform consecutive fast charging of batteries



Related products

Other

User manual

Parts drawing

Battery XGT® 2,5 Ah

BL4025

Li-ion • 40V max • 2,5 Ah • BL4025

Li-ion battery for 40V max tools

A 2,5 Ah Li-ion battery with a charge level indicator. Powerful general-use battery for 40V max Makita XGT® tools. Ideal for tools with a high power consumption. Charge time approximately 28 minutes with a rapid charger.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Capacity	2,5 Ah
Energy Capacity	90 Wh
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Average Charging Time	28 min
Product Dimensions (L x W x H):	118 x 77 x 65 mm
Product net weight	0,71 kg

User benefits

- Battery level indicator



Related products

 Other

User manual