

Circular Saw XGT® , 40Vmax, 5 200 min⁻¹, 165 mm

HS012GZ01



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	5200 min ⁻¹
Max. Cutting Depth at 90°	57 mm
Max. Cutting Depth at 45°	41 mm
Max. Bevel Range (Left)	0 - 50 °
Blade Diameter	165 mm
Bore Size (Arbor Diameter)	20 / 30 mm
Electronic brake	✓
AWS ready	✓
Sound Power Level (L _{WA})	102 dB(A)
Sound Pressure Level (L _{pA})	94 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Cutting Wood	≤ 2,5 m/s ²

EAN 0088381776639

Link to product - www.makita.uk.com

User benefits

- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- Electric brake for maximum productivity and increased operator safety
- Brushless maintenance-free and long-life motor
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth



Related products

■ Standard AC

164095-8
Parallel Guide



196961-1
Dust Nozzle 35 / 40 Mm



783203-8
Hex Wrench 5 Mm



821551-8
Makpac case (3)



■ Other

User manual

Parts drawing