



Technical Data

Weatherproof 13 Amp Switched Fused Connection Unit


Brief product description:

IP rated accessories designed to protect against ingress from water jets and dust, with durable seals that maintain integrity and a robust polycarbonate housing for high impact resistance which will not crack or fade, ensuring longevity of life.

Features:


- IP66 rated when in use
- Angled colour coded terminals with captive screws
- Flexible membrane: Allows easy switch and power status indication without compromising IP rating
- Hinged cover with fixing screw provides access to the fuse
- Fast fix - no separate screws, no screw covers, 150° rotation
- Multiple gland entry positions: 5 versatile entry options with M25 capability with an easy push out blank plug design. 1 drill out entry 20/25mm in rear face

Product Images



WP53

Line Diagrams



WP53



Weatherproof 13 Amp Switched Fused Connection Unit

Technical Specifications

Standard(s)	BS 1363-4	
Rating	3,120 Watts Max, 13Amp 250V AC	
Terminal Capacity	3 x 2.5mm ² , 2 x 4.0mm ² & 1 x 6.0mm ²	
Switch Type	Double Pole	
IP Rating	IP66	
RoHS Directive	Yes	
WEEE Directive	Yes	
Number of cable entries	5 x 20mm. 1 in each of 3 sides and 2 in the remaining side 1 drill out entry 20/25mm in rear face	

Packaging Information

Cat No.	Description	Packaging Type			Pack Quantity			Barcode		
		Product	Inner Box	Outer Box	Each	Inner Box	Outer Box	Individual	Inner Box	Outer Box
WP53	Switched FCU	Printed Box	/	Carton	1	/	10	5050765022330	/	5050765022361

Weights & Dimensions

Cat No.	Description	Dimensions (H x W x D) cm			Weight (kg)			CBM (m ³)
		Unpacked Product	Packed Product	Outer Box	Unpacked Product	Packed Product	Outer Box	Outer Box
WP53	Switched FCU	11.5 x 11.5 x 6.3	14.7 x 12.2 x 7.2	13.6 x 28.3 x 37.3	0.34	0.39	4.17	0.01436