

Impact Driver CXT®

TD110DZ

12Vmax • 1/4" • 110 Nm • 0 – 2
600 min⁻¹

Impact driver for tight spaces

A compact and light impact wrench with a hex. 1/4" drive shank. A small and light tool that is easy to use but offers a high fastening torque of up to 110 Nm. A handy LED light for added lighting. Tool only, battery and charger not included.



Technical specifications

CXT Battery	✓
Nominal Battery Voltage	12 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 2600 min ⁻¹
Max Fastening Torque Impact Drill	110 Nm
Tightening Capacity Standard Bolt	M5 - M12
Impacts per Minute (IPM)	0 - 3500 min ⁻¹
Driving Shank	1/4 "
Sound Power Level (L _{WA})	105 dB(A)
Sound Pressure Level (L _{pA})	94 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of the Tool	8,0 m/s ²
Vibration Uncertainty (K Factor),	1,5 m/s ²

User benefits

- Ideal for working in tight spaces and overhead applications
- The rubber coating on the handle ensures a firm working grip
- Quick mount for 1/4 "screwdriver
- LED light illuminates the work site
- Electric brake for maximum productivity and increased operator safety
- Battery protection system automatically shuts off power when the battery level is low




EAN 0088381800570

Link to product - www.makitauk.com







Related products

Standard AC

266622-8 Truss Head Screw M4 X 12		346909-5 Belt Hook	
784244-7 Screw Bit, Ph2 – Ph2, 50 Mm, Double			

Optional AC

784244-7 Screw Bit, Ph2 – Ph2, 50 Mm, Double		838312-9 Makpac Type 1 Inlay	
821549-5 Makpac case (1)		266622-8 Truss Head Screw M4 X 12	

Other

User manual

Parts drawing