



Rotary Hammer

HR2630/1

800 W • SDS-PLUS • 26 mm • 2.4 J

Professional three-mode rotary hammer

Efficient rotary hammer compatible with SDS-PLUS bits. Suitable for impact and unstressed drilling, plus chipping. Motor capacity of 800 W and speed can be adjusted between 0 and 1 200 min⁻¹ from a switch. Impact energy of 2.4 J and optimal drilling range of 8 – 18 mm in concrete. Max. drilling capacity of 26 mm in concrete.

Technical specifications

Power Supply Cord	2,5 m
Continuous Input Power 240V	800 W
Max Output Power	550 W
No load speed	0 - 1200 min ⁻¹
Impacts per Minute (IPM)	0 - 4600 min ⁻¹
Max. Drilling Diameter in Wood	32 mm
Max. Drilling Diameter in Concrete	26 mm
Max. Drilling Diameter in Steel	13 mm
Optimum Drilling Diameter Range in Concrete	4 - 18 mm
Impact Energy	2,4 J
Drilling diameter with TCT core bit	68 mm
Adapted for SDS-PLUS bits	✓
Sound Power Level (L _{WA})	101 dB(A)
Sound Pressure Level (L _{pA})	93 dB(A)

User benefits

- Same speed and torque in both directions with reverse gear
- The rubber coating on the handle ensures a firm working grip
- Torque limiter stops rotation if bit jams for increased operator safety and enhanced motor protection
- 3-Mode operation for "Rotation Only", "Hammering with Rotation" or "Hammering Only" for multiple applications
- Depth gauge for increased drilling consistency
- Variable speed control dial enables user to match the speed to the application for greater versatility

EAN 0088381687294

Link to product - www.makitauk.com



Related products

■ Standard AC

331886-4
Depth Gauge

821550-0
Makpac case (2)



■ Other

User manual

Parts drawing