



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

SAFETY DATA SHEET

SCRUBB Black Spot Remover

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Trade name: SCRUBB Black Spot Remover

Product no.: S69

Unique formula identifier (UFI): 4200-U0CW-6001-QY62

1.2. Relevant identified uses of the substance or mixture and uses advised against

Relevant identified uses of the substance or mixture: Cleaning product

Uses advised against : None known.

1.3. Details of the supplier of the safety data sheet

Company and address: Orca Hygiene
Blackhouse Circle,
Blackhouse Industrial Estate,
AB42 1BN Peterhead
United Kingdom
Tel: +44 (0)1779 871945

E-mail: technical@orcahygiene.com

Revision: 12/02/2025

SDS Version: 3.0

Date of previous version: 21/06/2024 (2.0)

1.4. Emergency telephone number

Healthcare professionals: Dial 0344 892 0111 to reach The National Poisons Information Service (NPIS) (24 hour service)

General public:

England - Dial 111 to reach NHS 111 (24 hour service)

Scotland - Dial 112 to reach NHS 24 (24 hour service)

Wales - Dial 111 or 0845 4647 to reach NHS Direct (24 hour service)

See section 4 "First aid measures".

SECTION 2: HAZARDS IDENTIFICATION

Classified according to Regulation (EC) No. 1272/2008 (CLP) as retained and amended in UK law.

2.1. Classification of the substance or mixture

Met. Corr. 1; H290, May be corrosive to metals.

Skin Corr. 1B; H314, Causes severe skin burns and eye damage.

2.2. Label elements

Hazard pictogram(s):



Signal word:

Danger

Hazard statement(s):

May be corrosive to metals. (H290)
Causes severe skin burns and eye damage. (H314)

Precautionary statement(s):

General: Keep out of reach of children. (P102)
If medical advice is needed, have product container or label at hand. (P101)

Prevention: Do not breathe vapour/mist. (P260)
Wear eye protection/protective gloves. (P280)

Response: IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower. (P303+P361+P353)
IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. (P305+P351+P338)

Storage: Store locked up. (P405)

Disposal: Dispose of contents/container in accordance with local regulation (P501)

Hazardous substances:

sodium hypochlorite, solution ... % Cl active
sodium hydroxide

Additional labelling:

UFI: 4200-U0CW-6001-QY62

Labelling of contents according to Detergents Regulation (EC) No 648/2004 as retained and amended in UK law:

>5% - <15%
· Chlorine-based bleaching Agents
< 5%
· Anionic surfactants
· Non-ionic surfactants

2.3. Other hazards

Additional warnings:

This mixture/product does not contain any substances known to fulfil the criteria for PBT and vPvB classification.
This product does not contain any substances considered to be endocrine disruptors in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2023/707.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1. Substances

Not applicable. This product is a mixture.

3.2. Mixtures

Product/substance	Identifiers	% w/w	Classification	Note
sodium hypochlorite, solution ... % Cl active	CAS No.: 7681-52-9 EC No.: 231-668-3	5-10%	EUH031 Skin Corr. 1B, H314	

	UK-REACH: Index No.: 017-011-00-1		Aquatic Acute 1, H400 (M=1)	
sodium hydroxide	CAS No.: 1310-73-2 EC No.: 215-185-5 UK-REACH: Index No.: 011-002-00-6	1-3%	Met. Corr. 1, H290 Skin Corr. 1A, H314 Eye Dam. 1, H318	

See full text of H-phrases in section 16. Occupational exposure limits are listed in section 8, if these are available.

Other information

SECTION 4: FIRST AID MEASURES

4.1. Description of first aid measures

- General information:** In the case of accident: Contact a doctor or casualty department – take the label or this safety data sheet.
Contact a doctor if in doubt about the injured person's condition or if the symptoms persist. Never give an unconscious person water or other drink.
- Inhalation:** Upon breathing difficulties or irritation of the respiratory tract: Bring the person into fresh air and stay with him/her.
- Skin contact:** Flush exposed area with water for a long time - at least 30 minutes. It may be necessary to flush for several hours. Use a comfortable water temperature (20-30 °C). Contact Poison Information/doctor/hospital for further advice on follow-up and treatment.
Remove contaminated clothing and shoes immediately. Ensure to wash exposed skin thoroughly with water and soap. Skin cleanser can be used. DO NOT use solvents or thinners.
If skin irritation occurs: Get medical advice/attention.
- Eye contact:** If in eyes: Flush eyes with plenty of water or salt water (20-30 °C) for at least 30 minutes and continue until irritation stops. Remove contact lenses. Make sure you flush under the upper and lower eyelids. Seek medical assistance immediately and continue flushing during transport.
- Ingestion:** In the case of ingestion, contact a doctor immediately. If the person is conscious, give them water. DO NOT try to induce vomiting unless this is recommended by a doctor. Hold head facing down to prevent vomit from returning to the mouth and throat. Prevent shock by keeping the injured person warm and calm. Initiate immediate resuscitation if breathing stops. If unconscious, roll the injured person into recovery position. Call an ambulance.
- Burns:** Not applicable.

4.2. Most important symptoms and effects, both acute and delayed

Tissue-damaging effects: This product contains substances with skin corrosive properties. Inhaled vapour or aerosols may produce adverse effects to lungs, irritations and burns in the respiratory organs as well as coughing. Dermal contact and contact with the eye cause irreversible effects.

4.3. Indication of any immediate medical attention and special treatment needed

IF exposed or concerned:
Get immediate medical advice/attention.

Information to medics

Bring this safety data sheet or the label from this product.

SECTION 5: FIREFIGHTING MEASURES

5.1. Extinguishing media

Suitable extinguishing media: Alcohol-resistant foam, carbon dioxide, powder, water mist.
Unsuitable extinguishing media: Waterjets should not be used, since they can spread the fire.

5.2. Special hazards arising from the substance or mixture

Fire will result in dense smoke. Exposure to combustion products may harm your health. Closed containers, which are exposed to fire, should be cooled with water. Do not allow fire-extinguishing water to enter the sewage system and nearby surface waters.

If the product is exposed to high temperatures, e.g. in the event of fire, dangerous decomposition compounds are produced. These are:

Halogenated compounds
Some metal oxides
Oxygen, hypochlorous acid, chlorine.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and protective clothing to prevent contact. Upon direct exposure contact The National Poisons Information Service (dial 111, 24 h service) in order to obtain further advice.

Hazchem Code: 2R

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Avoid direct contact with spilled substances.
Contaminated areas may be slippery.

6.2. Environmental precautions

Avoid discharge to lakes, streams, sewers, etc.
Keep unauthorized persons away from the spill

6.3. Methods and material for containment and cleaning up

Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations.
Wherever possible cleaning should be performed with normal cleaning agents. Avoid use of solvents.

6.4. Reference to other sections

See section 13 "Disposal considerations" on handling of waste.
See section 8 "Exposure controls/personal protection" for protective measures.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Avoid direct contact with the product.
Smoking, drinking and consumption of food is not allowed in the work area.

See section 8 "Exposure controls/personal protection" for information on personal protection.

7.2. Conditions for safe storage, including any incompatibilities

Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Store in a container with a resistant inner liner.

Recommended storage material: Always store in containers of the same material as the original container.

Storage conditions: No specific requirements

Incompatible materials: Strong acids, alkali metals, metal powders, oxidizing materials and amines. Contact with metals can result in decomposition with the formation of oxygen.

7.3. Specific end use(s)

This product should only be used for applications quoted in section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

No substances are listed in the national list of substances with an occupational exposure limit.

DNEL

sodium hydroxide

Duration:	Route of exposure:	DNEL:
Long term – Local effects - General population	Inhalation	1 mg/m ³
Long term – Local effects - Workers	Inhalation	1 mg/m ³

PNEC

No data available.

8.2. Exposure controls

Apply general control to prevent unnecessary exposure

General recommendations: Smoking, drinking and consumption of food is not allowed in the work area.

Exposure scenarios: There are no exposure scenarios implemented for this product.

Exposure limits: Occupational exposure limits have not been defined for the substances in this product.

Appropriate technical measures: Ensure that eyewash stations and safety showers are located within easy reach.
Apply standard precautions during use of the product. Avoid inhalation of vapours.

Hygiene measures: In between use of the product and at the end of the working day all exposed areas of the body must be washed thoroughly. Pay special attention to hands, forearms and face.

Measures to avoid environmental exposure: Keep damming materials near the workplace. If possible, collect spillage during work.

Individual protection measures, such as personal protective equipment


Generally: Use only UKCA marked protective equipment.

Respiratory Equipment:
No specific requirements


Skin protection:

Recommended	Type/Category	Standards	
No specific requirements.	-	-	

Hand protection:

Material	Glove thickness (mm)	Breakthrough time (min.)	Standards	
Gloves	-	-	EN374	

Eye protection:

Type	Standards	
Safety glasses	EN166	

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical state:	Liquid
Colour:	Colourless
Odour / Odour threshold:	Chlorine
pH:	12.5
Density (g/cm³):	-
Relative density:	1.05 (20 °C)
Kinematic viscosity:	No data available.
Particle characteristics:	Does not apply to liquids.

Phase changes

Melting point/Freezing point (°C):	No data available.
Softening point/range (°C):	Does not apply to liquids.
Boiling point (°C):	No data available.
Vapour pressure:	No data available.
Relative vapour density:	No data available.
Decomposition temperature (°C):	No data available.

Data on fire and explosion hazards

Flash point (°C):	No data available.
Flammability (°C):	No data available.
Auto-ignition temperature (°C):	No data available.

Lower and upper explosion limit (% v/v): No data available.

Solubility

Solubility in water: No data available.

n-octanol/water coefficient (LogKow): No data available.

Solubility in fat (g/L): No data available.

9.2. Other information

Oxidizing properties: No data available.

Other physical and chemical parameters: No data available.

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

Contact with acids liberates toxic gas.

Reacts violently with alkali metals, metal powders, oxidizing materials and amines.

10.2. Chemical stability

The product is stable under the conditions, noted in section 7 "Handling and storage".

10.3. Possibility of hazardous reactions

Contact with acids liberates toxic gas.

10.4. Conditions to avoid

Protect from sunlight. Do not expose to temperatures exceeding 20 °C/68 °F.

10.5. Incompatible materials

Strong acids, alkali metals, metal powders, oxidizing materials and amines. Contact with metals can result in decomposition with the formation of oxygen.

10.6. Hazardous decomposition products

Oxygen, hypochlorous acid, chlorine.

Thermal decomposition may produce corrosive vapours.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008 as retained and amended in UK law

Acute toxicity

Based on available data, the classification criteria are not met.

Skin corrosion/irritation

Causes severe skin burns and eye damage.

Serious eye damage/irritation

Causes serious eye damage.

Respiratory sensitisation

Based on available data, the classification criteria are not met.

Skin sensitisation

Based on available data, the classification criteria are not met.

Germ cell mutagenicity

Based on available data, the classification criteria are not met.

Carcinogenicity

Based on available data, the classification criteria are not met.

Reproductive toxicity

Based on available data, the classification criteria are not met.

STOT-single exposure

Based on available data, the classification criteria are not met.

STOT-repeated exposure

Based on available data, the classification criteria are not met.

Aspiration hazard

Based on available data, the classification criteria are not met.

11.2. Information on other hazards

Long term effects

Tissue-damaging effects: This product contains substances with skin corrosive properties. Inhaled vapour or aerosols may produce adverse effects to lungs, irritations and burns in the respiratory organs as well as coughing. Dermal contact and contact with the eye cause irreversible effects.

Endocrine disrupting properties

This mixture/product does not contain any substances known to have hormone-disrupting properties in relation to health.

Other information

None known.

SECTION 12: ECOLOGICAL INFORMATION

12.1. Toxicity

Product/substance	sodium hydroxide
Test method:	OECD 203
Species:	Fish, <i>Gambusia affinis</i>
Duration:	96 hours
Test:	LC50
Result:	125 mg/L

Product/substance	sodium hydroxide
Test method:	OECD 203
Species:	Fish, <i>Oncorhynchus mykiss</i>
Duration:	96 hours
Test:	LC50
Result:	45.5 mg/L

Product/substance	sodium hydroxide
Test method:	OECD 202
Species:	Daphnia, <i>Daphnia magna</i>
Duration:	48 hours
Test:	EC50
Result:	40-240 mg/L

12.2. Persistence and degradability

Based on available data, the classification criteria are not met.

12.3. Bioaccumulative potential

According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

Product/substance sodium hydroxide
Conclusion: No potential for bioaccumulation

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

This mixture/product does not contain any substances known to fulfil the criteria for PBT and vPvB classification.

12.6. Endocrine disrupting properties

This mixture/product does not contain any substances considered to have endocrine-disrupting properties in relation to the environment.

12.7. Other adverse effects

This product contains substances that are toxic to the environment. May result in adverse effects to aquatic organisms.

SECTION 13: DISPOSAL CONSIDERATIONS

Waste treatment methods

Product is covered by the regulations on hazardous waste.

HP 8 – Corrosive

Dispose of contents/container to an approved waste disposal plant.

Regulation (EU) No 1357/2014 of 18 December 2014 on waste as retained and amended in UK law.

EWC code


Not applicable.

Specific labelling

Contaminated packing

Packaging containing residues of the product must be disposed of similarly to the product.

SECTION 14: TRANSPORT INFORMATION

	14.1 UN / ID	14.2 UN proper shipping name	14.3 Hazard class(es)	14.4 PG*	14.5 Env**	Other informati on:
ADR	UN1719	CAUSTIC ALKALI LIQUID, N.O.S. (sodium hydroxide, sodium hypochlorite, solution ... % Cl active)	Transport hazard class: 8 Label: 8 Classification code: C5 	III	No	Limited quantities: 5 L Tunnel restriction code: (E) See below for additional informatio n.
IMDG	-	-	-	-	-	-
IATA	-	-	-	-	-	-

* Packing group

** Environmental hazards

▼ **Additional information**

This product is within scope of the regulations of transport of dangerous goods.

ADR / See Table A, section 3.2.1 for any information on special provisions, requirements, or warnings in connection with transport. See section 5.4.3, for instructions in writing regarding mitigation of damages in relation to incidents or accidents during transport.

Hazchem Code: 2R

14.6. Special precautions for user

Not applicable.

14.7. Maritime transport in bulk according to IMO instruments

No data available.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Restrictions for application: People under the age of 18 shall not be exposed to this product.

Demands for specific education: No specific requirements.

Control of Major Accident Hazards (COMAH) - Categories / dangerous substances: Not applicable.

Labelling of contents according to Detergents Regulation (EC) No 648/2004 as retained and amended in UK law:

- >5% - <15%
 - Chlorine-based bleaching Agents
- < 5%
 - Anionic surfactants
 - Non-ionic surfactants

Additional information: Tactile warning.
If this product is sold in retail, it must be delivered with child-resistant fastening.

Sources: The Management of Health and Safety at Work Regulations 1999.
Regulation (EC) No 648/2004 on detergents as retained and amended in UK law.
Regulation (EU) No 1357/2014 of 18 December 2014 on waste as retained and amended in UK law.
Regulation (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures (CLP) as retained and amended in UK law.
Regulation (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) as retained and amended in UK law.

15.2. Chemical safety assessment

No

SECTION 16: OTHER INFORMATION

Full text of H-phrases as mentioned in section 3

EUH031, Contact with acids liberates toxic gas.
H290, May be corrosive to metals.
H314, Causes severe skin burns and eye damage.
H318, Causes serious eye damage.
H400, Very toxic to aquatic life.

Abbreviations and acronyms

ADN = European Provisions concerning the International Carriage of Dangerous Goods by Inland Waterway
ADR = The European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE = Acute Toxicity Estimate
BCF = Bioconcentration Factor
CAS = Chemical Abstracts Service
CE = Conformité Européenne (European conformity)
CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
CSA = Chemical Safety Assessment
CSR = Chemical Safety Report
DMEL = Derived Minimal Effect Level
DNEL = Derived No Effect Level
EINECS = European Inventory of Existing Commercial chemical Substances
ES = Exposure Scenario
EUH statement = CLP-specific Hazard statement
EuPCS = European Product Categorisation System
EWC = European Waste Catalogue
GHS = Globally Harmonized System of Classification and Labelling of Chemicals
GWP = Global warming potential
IARC = International Agency for Research on Cancer (IARC)
IATA = International Air Transport Association
IBC = Intermediate Bulk Container
IMDG = International Maritime Dangerous Goods
LogPow = logarithm of the octanol/water partition coefficient
MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
OECD = Organisation for Economic Co-operation and Development
PBT = Persistent, Bioaccumulative and Toxic
PNEC = Predicted No Effect Concentration
RID = The Regulations concerning the International Carriage of Dangerous Goods by Rail
RRN = REACH Registration Number
SCL = A specific concentration limit
SVHC = Substances of Very High Concern
STOT-RE = Specific Target Organ Toxicity - Repeated Exposure
STOT-SE = Specific Target Organ Toxicity - Single Exposure
TWA = Time weighted average
UN = United Nations
UVBC = Unknown or variable composition, complex reaction products or of biological materials
VOC = Volatile Organic Compound
vPvB = Very Persistent and Very Bioaccumulative

Additional information

The classification of the substance/mixture in regard of health hazards are in accordance with the calculation methods given by Regulation (EC) No. 1272/2008 (CLP) as retained and amended in UK law.

The safety data sheet is validated by

OHL

Other

A change (in proportion to the last essential change (first cipher in SDS version, see section 1)) is marked



According to REACH Regulation (EC) No 1907/2006, as retained and amended by SI 2019/758 and SI 2020/1577

with a triangle.

The information in this safety data sheet applies only to this specific product (mentioned in section 1) and is not necessarily correct for use with other chemicals/products.

It is recommended to hand over this safety data sheet to the actual user of the product. Information in this safety data sheet cannot be used as a product specification.

Country-language: GB-en