



Impact Driver G - Series

TD127DZ

18V • 140 Nm • 0 – 2 300 min⁻¹

Compact brushless impact driver with assist mode and two power settings

A compact and light cordless impact driver. Max. torque of 140 Nm. Two power settings and assist mode for driving at low speed until commencing tightening. Handy LED light. Rubberised grip for convenient operating and electric brake for productivity and safety.

18V

Technical specifications

G-series	✓
Nominal Battery Voltage	18 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 2300 min ⁻¹
Max Fastening Torque Impact Drill	140 Nm
Tightening Capacity Standard Bolt	M5 - M14
Capacity machine screw	M4 - M8
Tightening Capacity High Tensile Bolt	M5 - M12
Impacts per Minute (IPM)	0 - 3000 min ⁻¹
Driving Shank	1/4 "
Sound Power Level (L _{WA})	104 dB(A)
Sound Pressure Level (L _{pA})	96 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of	8,5 m/s ²

User benefits

- Built-in LED light with pre-glow and afterglow functions illuminates the work area
- Variable speed trigger allows operator to adjust speed based on materials or application
- Ergonomic soft grip handle provides increased comfort
- Electric brake for maximum productivity and increased operator safety
- Battery protection circuit protects against overloading, over-discharging and over-heating

EAN 0088381633055

Link to product - www.makitauk.com



Related products