

Product Specification

256 GB m2 Series M.2 2280 PCIe NVMe SSD



The M2 Series M.2 PCIe NVMe SSDs are up to seven times faster in performance when compared to SATA SSDs and are compatible with most computing hardware and software that support the NVME standard, including small form factor machines (e.g Intel NUC), Ultrabooks and enthusiast desktops

- PCIe Gen3x4
- Compliant with PCI Express Base Specification Rev 3.1
- Compliant with NVMe 1.4
- Non-volatile Flash Memory for outstanding data retention
- Ultra-efficient Block Management and Wear Levelling
- Supports S.M.A.R.T. - Self-Monitoring, Analysis and Reporting Technology
- 5 year warranty or TBW - whichever is earlier applies

SKU	INSSD256GM280NM2
EAN	5055288447332

	Width (mm)	Depth (mm)	Height (mm)	Weight (g)
Product	22	80	2.25	10
Packaging	13.2	5.7	11.5	58

Capacity (GB)	256 GB
Component for	PC/Notebook
Form factor	M.2
Mean time between failures (MTBF) (hour)	1500000
TBW rating	128
Flash type	3D TLC
NVMe (Y/N)	Y
S.M.A.R.T. support (Y/N)	Y
TRIM support (Y/N)	Y
Read speed (MB per second)	3350
Write speed (MB per second)	1300
Random read (4KB) (Input/Output Operations Per Second)	179000
Random write (4KB) (Input/Output Operations Per Second)	140000
Operating voltage (Volt)	3.3
Power consumption (read) (Watt)	2789
Power consumption (write) (Watt)	2310
Hardware encryption (Y/N)	N

Interface	PCI Express 3.1
Operating temperature (T-T) (degrees Celcius)	0 - 70
Storage temperature (T-T) (degrees Celcius)	-40 - 85
Operating relative humidity (H-H) (percent)	5 - 95
Sustainability certificates	RoHS
Certification	CE, FCC, UKCA