



PRODUCT SPEC SHEET

SKU 216025

Model:VT-6060-N

EAN:3800157675970

VT-6060 40W LED PANEL 600x600mm 6500K SQUARE



IP20
STANDARD

02 YEAR
WARRANTY

Super Bright
120
LUMENS/W

- Powerful LED light source with lumen efficiency of 120 LM/W
- Strong and sturdy Aluminium + PMMA + PP body
- Fitted with high efficiency SMD LED Chips
- Easy to connect driver for quicker installation
- Compatible driver SKU 6614(Not Included)
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

TECHNICAL INFORMATION

On/Off Cycles:	>15000
Model:	VT-6060-N
Color Temperature:	6500K
CRI:	>80
Watts:	40
Lumens:	4950
Input Power:	AC:200-240V, 50/60Hz
Unit Color:	White
Color for Web:	White
Body Type:	Aluminium + PMMA + PP
Dimension:	595x595x12.5mm
Shape:	Square
PF:	>0.9
LED Chip Type:	SMD
Beam Angle:	110°

LISTING DETAILS

SKU:	216025
Model:	VT-6060-N
EAN:	3800157675970
Commodity Code:	94051190

PACKAGING

Gross Weight (Kgs):	2.47
Unit CBM:	0.010719
Dimension:	595x595x12.5mm

MASTER BOX PACKAGING

Box Qty:	6
Qty Per Pallet:	
Length (Box) mm:	650

Downward LOR (%):	100
ULR (%):	0
Energy Rating Label:	E (2021)
Retail Pack:	1pc
IP Rating:	IP20
Long Life:	25,000 Hours
lumens per watt:	120
EMC Certificate:	Check the certificate
LVD Certificate:	Check the certificate
ROHS Certificate:	Check the certificate

Width (Box) mm:	140
Height (Box) mm:	630