

UHZ35

Eco-friendly compact high brightness 4K UHD laser projector



- **Incredible True 4K UHD resolution and laser technology - HDR and HLG compatible**
- **Lights on viewing - bright 3500 lumens - Perfect for big screen home entertainment and immersive gaming**
- **Small form factor for easy installation - 1.6x zoom, 360-degree and portrait projection**
- **Lightning-fast gaming - Supports 1080p 240Hz at 4.4ms and 4K 60Hz at 17ms**



The UHZ35 is one of Optoma's most compact and hassle-free 4K UHD DuraCore laser projectors to date. Designed for maintenance-free continuous operation, it delivers powerful image performance with flexible installation features and extensive connectivity options in a sleek, compact form factor, up to 34% smaller than previous Optoma models.¹

An added benefit, the UHZ35 features an external power supply offering more reliability, portability and energy efficiency.

Specifications

UPC: 796435 81 542 4, EAN: 5055387668898, Colour: White



Display/image

Display technology	DLP™
Resolution	UHD (3840x2160)
Brightness	3,500 lumens
Contrast ratio	500,000:1
Native aspect ratio	16:9
Aspect ratio - compatible	4:3,16:9,16:10
Keystone correction - horizontal	+/-30°
Keystone correction - vertical	+/-30°
Displayable colours (millions)	1073.4
Horizontal scan rate	15 ~ 140Khz
Vertical scan rate	24 ~ 240Hz
Uniformity	80%
Screen size	0.66m ~ 7.7m (26" ~ 303") diagonal

Lamp info

Light source type	Laser
LASER life	30,000 hours

Optical

Throw ratio	1.4:1 ~ 2.24:1
Projection distance (m)	1.3m - 9.4m
Zoom	1.6
Zoom type	Manual
Focal length (mm)	20.91 ~ 32.62
Native offset	116%

Connectivity

Connections	Inputs 1 x HDMI 2.0, 1 x HDMI 2.0 (eARC) Outputs 1 x Audio 3.5mm, 1 x USB-A power 1.5A Control 1 x RJ45, 1 x RS232
-------------	---

General

Noise level (min)	28dB
Noise level (max)	35dB
PC compatibility	UHD, FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac
2D compatibility	NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4,43MHz SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p, 576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz)
3D compatibility	Yes (DLP 3D; PC frame sequential 120Hz 3D, Blu-ray DVD 3D)
3D	Full 3D
Security	Security bar, Kensington Lock, Password protected interface
IP rating	IP6X
OSD / display languages	25 languages: Arabic, Czech, Danish, Dutch, English, Farsi, Finnish, French, German, Greek, Hungarian, Indonesian, Italian, Japanese, Norwegian, Polish, Portuguese, Romanian, Russian, Chinese (simplified), Spanish, Swedish, Chinese (traditional), Turkish, Vietnamese

24/7 operation

360° operation	Yes
Operating conditions	0°C ~ 40°C, Max. Humidity 80%, Max. Altitude 10,000ft

Remote control

Speaker count	Card style
Watts per speaker	1

In the box

AC power cord	15W
Remote control with 1x CR2025 Battery	
Basic user manual	

Input lag

4.40ms
UHDCast Pro

Power

Power supply	External power supply, 100V ~ 240V, 50-60Hz
Power consumption (standby)	<0.5W
Power consumption (min)	126W
Power consumption (max)	185W

Weight and dimensions

Dimensions (W x D x H) mm	274 x 216 x 114
Gross weight	4.2 kg
Net weight	3 kg