3-641229-5 ✔ ACTIVE


MTA 156




TE Internal #: 3-641229-5

5 Position, Receptacle, Connector Assembly, Insulation Displacement (IDC), Wire-to-Board, Gold (Au) / Gold Flash over Palladium Nickel, MTA 156

View on TE.com >

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**

Mating Alignment: **Without**

Connector & Housing Type: **Receptacle**

Mating Retention Type: **Locking Ramp**

Connector System: **Wire-to-Board**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Insertion Force Type	Normal
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Cavities	5
Contacts Preloaded	Yes
Number of Positions	5
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC

Body Features

Primary Product Color	Red

Contact Features

Contact Underplating Material	Nickel
Wire Contact Termination Area Plating Material	Tin
Contact Type	Receptacle
Contact Mating Area Plating Material	Gold (Au), Gold Flash over Palladium Nickel
Contact Retention Within Housing	With
Contact Current Rating (Max)	7 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)

Mechanical Attachment

Contact Retention Type Within Housing	Locking Lance
Mating Alignment	Without
Mating Retention Type	Locking Ramp
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon 6/6
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Connector Width	9.78 mm[.385 in]
Connector Height	18.42 mm[.725 in]
Wire Size	22 AWG
Connector Length	19.81 mm[.78 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Shielded	No
Circuit Application	Signal

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
UL Rating	Recognized
Compatible With Approved Standards Products	UL E28476
CSA Rating	LR 7189
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	250
Packaging Method	Bag/Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts




TE Part # 3-647174-5
05P MTA156 CONN ASSY W/O#4



TE Part # 3-644631-5
05P MTA156 HDR ASSY STR LF



TE Part # 643495-3
05P MTA156 HDR ASSY W/O#2



TE Part # 643495-1
05P MTA156 HDR ASSY W/O#4




TE Part # 643067-5
05P MTA156 MOLDED COVER




TE Part # 643495-4
05P MTA156 HDR ASSY W/O#3




TE Part # 3-641202-5
05P MTA156 HDR ASSY PL 30AU LF



TE Part # 3-644760-5
05P MTA156 HDR ASSY FL ST LF



TE Part # 3-641209-5
05P MTA156 HDR ASSY FL ST LF



TE Part # 3-641210-5
05P MTA156 HDR FLRA FB 30AU LF




TE Part # 643495-2
05P MTA156 HDR ASSY W/O#2&4




TE Part # 58074-1
MTA 50/100/156 MANUAL TOOL FRAME




TE Part # 640551-5
05P MTA156 COVER



TE Part # 3-644759-5
05P MTA156 HDR ASSY STR LF




TE Part # 643071-5
05P MTA156 FD-THRU COVER



TE Part # 3-644633-5
05P MTA156 HDR ASSY R/A LF



TE Part # 3-644761-5
05P MTA156 HDR ASSY R/A F/L LF



TE Part # 3-641208-5
05P MTA156 HDR ASSY FL ST LF



TE Part # 640643-5
05P MTA156 COVER F/T


Also in the Series | MTA 156



Connector Caps & Covers(89)




Connector Contacts(4)




Connector Hardware(2)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(677)



Power Contacts(3)



Rectangular Power Connectors(1178)




Wire-to-Board Headers & Receptacles (677)

Customers Also Bought



TE Part #31264
BUDG R 22-16 COMM 22-18 MIL 6



TE Part #8-42844-1
RECEPT,PIDG FASTON 14-12 250



TE Part #66507-4
HD 20 DF PIN PLTD



TE Part #104257-9
10 MTE RCPT HSG SR LATCH .100



TE Part #2-111623-4
40, 2MM, POL,30 DP, LEAD FREE




TE Part #172335-1
MINI UMNL PLUG HOUSING 1P



TE Part #3-640426-4
04P MTA156 CONN ASSY 18AWG ORA



TE Part #3-640426-6
06P MTA156 CONN ASSY 18AWG ORA



TE Part #6-1393114-9
KUHP-11A51-120=KU



TE Part #8-1393211-4
T92S11A22-120

Documents

Product Drawings

05P MTA156 CONN ASSY 22AWG LF

English

CAD Files

Customer View Model

ENG_CVM_CVM_3-641229-5_S.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-641229-5_S.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-641229-5_S.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Application Specification

English

Application Specification

Japanese

Application Specification

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

English

MTA 156 Ribbon Cable Connector Assemblies (English And Spanish)

Japanese