

3 HOURS LED EMERGENCY EMERGENCY BULKHEAD

3W

Maintained/Non-Maintained



FEATURES:

- Maintained/Non-maintained
- 3 hour emergency operation
- Push-fit connector and hinged gear tray for speedy installation
- Energy efficient at 100lm per Watt
- Multiple cable entry position
- Lightweight but with robust polycarbonate construction



APPLICATIONS



COMMERCIAL



FACTORIES




WASHROOMS

5W

3 HOURS LED EMERGENCY EMERGENCY BULKHEAD

Maintained/Non-Maintained

Part No.	243014
DESCRIPTION	3W LED Emergency Bulkhead Daylight (6500K) 300lm
DIMENSIONS	355 x 110 x 69.8mm
COLOUR	6500K (Daylight White)
CURRENT	650mA
LED TYPE	2835 SMD
COLOUR RENDITION (CRI)	Ra>80
LUMENS	300lm
IP RATING	IP65
BEAM ANGLE	120°
CONSTRUCTION	Polycarbonate
WORKING TEMPERATURES	-20°C to +40°C
ENERGY CONSUMPTION	3 kWh
CERTIFICATION	CE, RoHS
WARRANTY	1 year (+ 4 years extended warranty with online registration) Battery 3 years only
BUILDING REGS - PART L	Yes

**BRIGHT SOURCE****F**

Formerly rated A+
(same quality,
new energy rating
label regulations)

