

PX130&PX140

DESCRIPTION

- Industrial protective glove.
- Synthetic coating on a synthetic textile liner.
- Available in grey (PX130) or in white (PX140).
- 5 available sizes : 6, 7, 8, 9 and 10.
- Single pair packed, trade unit 12 pairs, 240 pairs in a transit case.

CHARACTERISTICS

- Nylon textile liner made with a seamless non-stop process.
- Fine and stretchable stitches.
- Lightweight ergonomic design.
- Flat dipped polyurethane palm fit coating.
- Latex knit wrist to ensure snug fit.

PERFORMANCES

- Excellent adaptability owing to its extensibility.
- Excellent comfort and dexterity.
- Ventilated back ensures that the hand can breathe naturally.
- Good abrasion resistance.
- In compliance with the standards EN420 (General Requirements) and EN388 (Mechanical Hazards) by the notified body CTC.

APPLICATIONS

- For general handlings where comfort is required.
- Ideal for use in automotive industry, painting, print shops, general maintenance, small parts handling.

LIMITATIONS

- Do not use for handling liquids and pointed objects.
- Do not use with a rotating machine in which glove may get caught.
- Limited protection at the wrist.



This glove is certified to comply with the essential requirements of European Directive EEC/89/686 of December 21st, 1989 relative to personal protective equipment submitted to CE type examination issued by a notified laboratory, who certifies the conformity of this glove with the EN standards to which it responds and certifies the performance levels obtained during tests.



EN 420

EN 420

5 Dexterity

EN 388

4 Abrasion

1 Cut

3 Tear

1 Puncture



EN 388

Mechanical hazards

Order codes

| Sizes | 6 (XS) | 7 (S) | 8 (M) | 9 (L) | 10 (XL) |
|-------|--------|--------|--------|--------|---------|
| PX130 | M10254 | M10255 | M10256 | M10257 | M10258 |
| PX140 | M10249 | M10250 | M10251 | M10252 | M10253 |