



SPECIFICATIONS

Marketing Name	GeForce RTX™ 5060 8G VENTUS 2X OC
Model Name	G5060-8V2C
Graphics Processing Unit	NVIDIA® GeForce RTX™ 5060
Cores	3840 Units
Memory	8GB GDDR7
Power connectors	8-pin x1
Memory Interface	128-bit
Core Clocks	Extreme Performance: 2535 MHz (MSI Center) Boost: 2527 MHz
Memory Speed	28 Gbps
Maximum Displays	4
Digital Maximum Resolution	7680 x 4320
Output	DisplayPort x 3 (v2.1b) HDMI™ x 1 (As specified in HDMI™ 2.1b: up to 4K 480Hz or 8K 120Hz with DSC, Gaming VRR, HDR)
Power consumption (W)	145 W
Recommended Power Supply (W)	550 W
DirectX Version Support	12 Ultimate
Card Dimension(mm)	197 x 120 x 41 mm
Weight	511 g / 829 g

CONNECTIONS



1. DisplayPort
2. HDMI™

FEATURES

Dual Fan



Two fans and a huge heatsink ensure a cool and quiet experience for you.

TORX FAN 5.0



Fan blades linked by ring arcs and a fan cowl work together to stabilize and maintain high-pressure airflow.

Reinforcing Backplate



The reinforcing backplate features a flow-through design that provides additional ventilation.

Zero Frozr



The fans completely stop when temperatures are relatively low, eliminating all noise.

Fuse



Additional fuses built into the custom PCB provide additional safeguards against electrical damage.

DrMOS



DrMOS power stage solutions provide great efficiency with low power loss and enhanced voltage controls.

MSI Center



The exclusive MSI Center software lets you monitor, tweak and optimize MSI products in real-time.

Afterburner



Take full control with the most recognized and widely used graphics card overclocking software in the world.